

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858743

Luminaire Tested: **LD4C35W2N2765D010 4LBMLI_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2765D010 4LBMLI_5000K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2765 LEDS
AND 4LBMLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3526.0 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858743

CATALOG NUMBER: LD4C35W2N2765D010 4LBMLI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858743

CATALOG NUMBER: LD4C35W2N2765D010 4LBMLI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	107	111	109	107	105		105	103	102			101	100	99			98
2	109	104	100	97	107	102	99	96		99	96	94			96	94	92			94
3	104	98	93	89	102	96	92	89		94	90	87			91	88	86			89
4	99	92	87	83	97	91	86	82		89	85	81			87	83	80			85
5	94	87	81	77	93	86	81	77		84	79	76			82	78	75			81
6	90	82	76	72	89	81	76	72		80	75	71			78	74	71			77
7	86	77	72	68	85	77	71	68		75	71	67			74	70	67			73
8	82	73	68	64	81	73	67	64		72	67	64			71	66	63			70
9	79	70	64	60	78	69	64	60		68	63	60			67	63	60			67
10	75	66	61	57	74	66	61	57		65	60	57			64	60	57			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	682881
5°	671283
10°	616795
15°	516533
20°	413825
25°	332500
30°	247516
35°	141398
40°	66363
45°	28181
50°	8964
55°	4562
60°	3145
65°	2471
70°	1545
75°	0
80°	0
85°	0



TEST NUMBER: P858743

CATALOG NUMBER: LD4C35W2N2765D010 4LBMLI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	503.3	14.3
10°-20°	1125.2	31.9
20°-30°	1118.7	31.7
30°-40°	609.2	17.3
40°-50°	140.8	4.0
50°-60°	19.8	0.6
60°-70°	7.4	0.2
70°-80°	1.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2747.1	77.9
0°-40°	3356.3	95.2
0°-60°	3516.9	99.7
0°-90°	3526.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3526.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5558	
5°	5443	503
15°	4061	1125
25°	2453	1119
35°	943	609
45°	162	141
55°	21	20
65°	8	7
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P858743

CATALOG NUMBER: LD4C35W2N2765D010 4LBMLI_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	5558.5
2.5°	5545.7
5°	5443.3
7.5°	5234.3
10°	4944.3
12.5°	4517.7
15°	4061.2
17.5°	3609.0
20°	3165.3
22.5°	2802.7
25°	2452.9
27.5°	2120.2
30°	1744.8
32.5°	1326.8
35°	942.8
37.5°	635.5
40°	413.8
42.5°	260.2
45°	162.2
47.5°	93.9
50°	46.9
52.5°	25.6
55°	21.3
57.5°	12.8
60°	12.8
62.5°	8.5
65°	8.5
67.5°	4.3
70°	4.3
72.5°	4.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)