

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858756

Luminaire Tested: **LD4C35W2N2765D010 4LBNLI_6500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2765D010 4LBNLI_6500K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 6500K, W2N2765 LEDS
AND 4LBNLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2857.0 lumens
Efficiency: N/A
Efficacy: 54.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858756

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P858756

CATALOG NUMBER: LD4C35W2N2765D010 4LBNI_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90		
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73		
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66		
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63		
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	903256
5°	812833
10°	630118
15°	456081
20°	315797
25°	230225
30°	167280
35°	98984
40°	41633
45°	12978
50°	1682
55°	942
60°	1081
65°	1279
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858756

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	579.4	20.3
10°-20°	991.9	34.7
20°-30°	788.3	27.6
30°-40°	417.3	14.6
40°-50°	71.9	2.5
50°-60°	5.4	0.2
60°-70°	2.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2359.7	82.6
0°-40°	2777.0	97.2
0°-60°	2854.3	99.9
0°-90°	2857.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2857.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7352	
5°	6591	579
15°	3586	992
25°	1698	788
35°	660	417
45°	75	72
55°	4	5
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858756

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	7352.3
2.5°	7163.0
5°	6591.1
7.5°	5843.2
10°	5051.1
12.5°	4285.6
15°	3585.9
17.5°	2934.7
20°	2415.5
22.5°	2019.5
25°	1698.4
27.5°	1438.8
30°	1179.2
32.5°	915.2
35°	660.0
37.5°	435.7
40°	259.6
42.5°	149.6
45°	74.7
47.5°	26.4
50°	8.8
52.5°	8.8
55°	4.4
57.5°	4.4
60°	4.4
62.5°	4.4
65°	4.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)