

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858763

Luminaire Tested: **LD4C35W2N2765D010 4LBWH_2700K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2765D010 4LBWH_2700K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, W2N2765 LEDS
AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2723.0 lumens
Efficiency: N/A
Efficacy: 51.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858763

CATALOG NUMBER: LD4C35W2N2765D010 4LBWH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P858763

CATALOG NUMBER: LD4C35W2N2765D010 4LBWH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	215620
5°	216444
10°	217100
15°	217121
20°	215927
25°	210868
30°	197085
35°	170673
40°	133319
45°	95662
50°	62135
55°	37205
60°	21770
65°	13982
70°	9303
75°	7025
80°	5235
85°	0



TEST NUMBER: P858763

CATALOG NUMBER: LD4C35W2N2765D010 4LBWH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.1	6.1
10°-20°	481.6	17.7
20°-30°	710.7	26.1
30°-40°	701.3	25.8
40°-50°	429.2	15.8
50°-60°	164.5	6.0
60°-70°	51.5	1.9
70°-80°	15.1	0.6
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1359.4	49.9
0°-40°	2060.7	75.7
0°-60°	2654.5	97.5
0°-90°	2723.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2723.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1755	
5°	1755	167
15°	1707	482
25°	1556	711
35°	1138	701
45°	551	429
55°	174	165
65°	48	51
75°	15	15
85°	0	2
90°	0	



TEST NUMBER: P858763

CATALOG NUMBER: LD4C35W2N2765D010 4LBWH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1755.1
2.5°	1758.8
5°	1755.1
7.5°	1751.4
10°	1740.3
12.5°	1725.5
15°	1707.1
17.5°	1684.9
20°	1651.6
22.5°	1614.8
25°	1555.6
27.5°	1481.6
30°	1389.3
32.5°	1274.8
35°	1138.0
37.5°	986.5
40°	831.3
42.5°	687.3
45°	550.6
47.5°	428.5
50°	325.1
52.5°	240.2
55°	173.7
57.5°	121.9
60°	88.6
62.5°	66.6
65°	48.1
67.5°	37.0
70°	25.9
72.5°	18.5
75°	14.8
77.5°	7.4
80°	7.4
82.5°	3.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)