

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858773

Luminaire Tested: **LD4C35W2N2765D010 4LBWLI_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2765D010 4LBWLI_5000K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2765 LEDS
AND 4LBWLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3721.0 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858773

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858773

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	280081
5°	284839
10°	297713
15°	315997
20°	329839
25°	326969
30°	304075
35°	260134
40°	198190
45°	116250
50°	49674
55°	14629
60°	4202
65°	2471
70°	1545
75°	2041
80°	0
85°	0



TEST NUMBER: P858773

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.0	6.0
10°-20°	703.6	18.9
20°-30°	1097.6	29.5
30°-40°	1068.0	28.7
40°-50°	533.4	14.3
50°-60°	82.6	2.2
60°-70°	10.0	0.3
70°-80°	2.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2024.2	54.4
0°-40°	3092.2	83.1
0°-60°	3708.2	99.7
0°-90°	3721.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3721.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2280	
5°	2310	223
15°	2484	704
25°	2412	1098
35°	1734	1068
45°	669	533
55°	68	83
65°	8	10
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P858773

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2279.8
2.5°	2288.4
5°	2309.7
7.5°	2343.8
10°	2386.5
12.5°	2441.8
15°	2484.5
17.5°	2518.6
20°	2522.9
22.5°	2493.0
25°	2412.1
27.5°	2292.6
30°	2143.5
32.5°	1956.1
35°	1734.5
37.5°	1491.4
40°	1235.8
42.5°	963.1
45°	669.1
47.5°	430.4
50°	259.9
52.5°	140.6
55°	68.3
57.5°	29.9
60°	17.1
62.5°	12.8
65°	8.5
67.5°	8.5
70°	4.3
72.5°	4.3
75°	4.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)