

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859068

Luminaire Tested: **LX4C55D010 EX4C559027 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C55D010 EX4C559027 4LBMH
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4267.0 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859068

CATALOG NUMBER: LX4C55D010 EX4C559027 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P859068

CATALOG NUMBER: LX4C55D010 EX4C559027 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	337884
5°	339175
10°	340215
15°	340226
20°	338363
25°	330426
30°	308841
35°	267438
40°	208919
45°	149904
50°	97379
55°	58281
60°	34104
65°	21889
70°	14584
75°	11012
80°	8207
85°	0



TEST NUMBER: P859068

CATALOG NUMBER: LX4C55D010 EX4C559027 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.9	6.1
10°-20°	754.7	17.7
20°-30°	1113.6	26.1
30°-40°	1099.0	25.8
40°-50°	672.5	15.8
50°-60°	257.8	6.0
60°-70°	80.6	1.9
70°-80°	23.7	0.6
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2130.3	49.9
0°-40°	3229.2	75.7
0°-60°	4159.6	97.5
0°-90°	4267.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4267.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2750	
5°	2750	262
15°	2675	755
25°	2438	1114
35°	1783	1099
45°	863	673
55°	272	258
65°	75	81
75°	23	24
85°	0	3
90°	0	



TEST NUMBER: P859068

CATALOG NUMBER: LX4C55D010 EX4C559027 4LBMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2750.3
2.5°	2756.1
5°	2750.3
7.5°	2744.5
10°	2727.2
12.5°	2704.0
15°	2675.0
17.5°	2640.2
20°	2588.1
22.5°	2530.4
25°	2437.6
27.5°	2321.7
30°	2177.1
32.5°	1997.7
35°	1783.2
37.5°	1545.9
40°	1302.7
42.5°	1077.0
45°	862.8
47.5°	671.5
50°	509.5
52.5°	376.5
55°	272.1
57.5°	191.0
60°	138.8
62.5°	104.3
65°	75.3
67.5°	58.0
70°	40.6
72.5°	29.0
75°	23.2
77.5°	11.6
80°	11.6
82.5°	5.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)