

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859093

Luminaire Tested: **LX4C55D010 EX4C559030 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P859093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C55D010 EX4C559030 4LBSH
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5794.0 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859093

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P859093

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	372271
5°	370548
10°	362906
15°	349714
20°	333617
25°	315637
30°	297734
35°	280336
40°	263959
45°	246052
50°	224363
55°	198146
60°	167720
65°	131685
70°	93967
75°	51502
80°	9056
85°	0



TEST NUMBER: P859093

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.8	4.9
10°-20°	771.5	13.3
20°-30°	1071.4	18.5
30°-40°	1169.1	20.2
40°-50°	1090.6	18.8
50°-60°	827.8	14.3
60°-70°	453.3	7.8
70°-80°	124.7	2.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2126.7	36.7
0°-40°	3295.8	56.9
0°-60°	5214.3	90.0
0°-90°	5794.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5794.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3030	
5°	3005	284
15°	2750	771
25°	2328	1071
35°	1869	1169
45°	1416	1091
55°	925	828
65°	453	453
75°	108	125
85°	0	2
90°	0	



TEST NUMBER: P859093

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBSH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3030.2
2.5°	3030.2
5°	3004.7
7.5°	2966.5
10°	2909.1
12.5°	2832.6
15°	2749.6
17.5°	2647.6
20°	2551.8
22.5°	2436.9
25°	2328.5
27.5°	2220.1
30°	2098.8
32.5°	1984.0
35°	1869.2
37.5°	1754.3
40°	1645.9
42.5°	1531.0
45°	1416.2
47.5°	1301.4
50°	1173.9
52.5°	1052.6
55°	925.1
57.5°	803.8
60°	682.6
62.5°	561.4
65°	453.0
67.5°	350.8
70°	261.6
72.5°	178.6
75°	108.5
77.5°	51.0
80°	12.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)