

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859653

Luminaire Tested: **LX4C08D010 EX4C089030 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P859653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089030 4LBMLI
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 825.0 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859653

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859653

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			99
2	109	105	102	99	107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	92	103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86	99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80	95	88	84	80		87	82	79			85	81	79			83
6	92	85	80	76	91	84	79	76		83	78	75			81	78	75			80
7	89	81	76	72	88	80	75	72		79	75	71			78	74	71			77
8	85	77	72	68	84	77	72	68		76	71	68			75	71	68			74
9	82	74	69	65	81	73	68	65		72	68	65			72	68	65			71
10	79	71	66	62	78	70	65	62		69	65	62			69	65	62			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	260830
5°	234720
10°	181958
15°	131702
20°	91190
25°	66476
30°	48303
35°	28586
40°	12028
45°	3753
50°	478
55°	278
60°	319
65°	378
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859653

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	20.3
10°-20°	286.4	34.7
20°-30°	227.6	27.6
30°-40°	120.5	14.6
40°-50°	20.8	2.5
50°-60°	1.6	0.2
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	681.4	82.6
0°-40°	801.9	97.2
0°-60°	824.2	99.9
0°-90°	825.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	825.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2123	
5°	1903	167
15°	1036	286
25°	490	228
35°	191	121
45°	22	21
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859653

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2123.1
2.5°	2068.4
5°	1903.3
7.5°	1687.3
10°	1458.6
12.5°	1237.5
15°	1035.5
17.5°	847.4
20°	697.5
22.5°	583.2
25°	490.4
27.5°	415.5
30°	340.5
32.5°	264.3
35°	190.6
37.5°	125.8
40°	75.0
42.5°	43.2
45°	21.6
47.5°	7.6
50°	2.5
52.5°	2.5
55°	1.3
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)