

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859097

Luminaire Tested: **LX4C55D010 EX4C559030 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C55D010 EX4C559030 4LBWLI
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5841.0 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859097

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P859097

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P859097

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBWL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	350.0	6.0
10°-20°	1104.5	18.9
20°-30°	1723.0	29.5
30°-40°	1676.5	28.7
40°-50°	837.4	14.3
50°-60°	129.6	2.2
60°-70°	15.7	0.3
70°-80°	4.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3177.5	54.4
0°-40°	4853.9	83.1
0°-60°	5820.9	99.7
0°-90°	5841.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5841.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3579	
5°	3626	350
15°	3900	1104
25°	3786	1723
35°	2723	1676
45°	1050	837
55°	107	130
65°	13	16
75°	7	4
85°	0	0
90°	0	



TEST NUMBER: P859097

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3578.8
2.5°	3592.1
5°	3625.6
7.5°	3679.2
10°	3746.2
12.5°	3833.0
15°	3899.9
17.5°	3953.5
20°	3960.2
22.5°	3913.3
25°	3786.4
27.5°	3598.8
30°	3364.7
32.5°	3070.6
35°	2722.7
37.5°	2341.2
40°	1939.9
42.5°	1511.9
45°	1050.3
47.5°	675.6
50°	408.0
52.5°	220.7
55°	107.2
57.5°	46.9
60°	26.8
62.5°	20.1
65°	13.4
67.5°	13.4
70°	6.7
72.5°	6.7
75°	6.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)