

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859670

Luminaire Tested: **LX4C08D010 EU4089035 4LBHYLI**

Issue Date: 7/20/2023



Test Information

Test Method: LM-79-08
Report Number: P859670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EU4089035 4LBHYLI
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 4LBHYP TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 704.0 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859670

CATALOG NUMBER: LX4C08D010 EU4089035 4LBHYLI

Luminous Intensity Polar Plot





TEST NUMBER: P859670

CATALOG NUMBER: LX4C08D010 EU4089035 4LBHYLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	83	79	76	90	83	79	76	82	78	75		81	78	75		80
9	88	81	76	73	87	80	76	73	79	76	73		79	75	73		78
10	85	78	74	71	84	78	73	71	77	73	70		76	73	70		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	267550
5°	260791
10°	221105
15°	143315
20°	88993
25°	47905
30°	16470
35°	6629
40°	1780
45°	799
50°	306
55°	150
60°	74
65°	87
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859670

CATALOG NUMBER: LX4C08D010 EU4089035 4LBHYLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.7	27.1
10°-20°	314.6	44.7
20°-30°	163.1	23.2
30°-40°	30.9	4.4
40°-50°	3.9	0.6
50°-60°	0.6	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	668.4	94.9
0°-40°	699.3	99.3
0°-60°	703.8	100.0
0°-90°	704.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	704.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2178	
5°	2115	191
15°	1127	315
25°	353	163
35°	44	31
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859670

CATALOG NUMBER: LX4C08D010 EU4089035 4LBHYLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2177.8
2.5°	2174.2
5°	2114.7
7.5°	1978.2
10°	1772.4
12.5°	1462.6
15°	1126.8
17.5°	855.6
20°	680.7
22.5°	507.5
25°	353.4
27.5°	217.2
30°	116.1
32.5°	78.3
35°	44.2
37.5°	19.2
40°	11.1
42.5°	7.2
45°	4.6
47.5°	2.6
50°	1.6
52.5°	0.7
55°	0.7
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)