

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859691

Luminaire Tested: **LD4C08D010 EU4089040 4LBHYH**

Issue Date: 10/18/2023



Test Information

Test Method: LM-79-08
Report Number: P859691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-7)
Test Lab: INNOVATION CENTER
Issue Date: 10/18/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08D010 EU4089040 4LBHYH
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND 4LCHYP TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 542.4 lumens
Efficiency: N/A
Efficacy: 54.8 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.59
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859691

CATALOG NUMBER: LD4C08D010 EU4089040 4LBHYH

Luminous Intensity Polar Plot





TEST NUMBER: P859691

CATALOG NUMBER: LD4C08D010 EU4089040 4LBHYH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	94	92		95	93	91		93
4	103	97	92	89	101	96	92	88	94	90	87		92	89	86		90
5	99	92	88	84	97	92	87	84	90	86	83		88	85	83		87
6	95	89	84	81	94	88	83	80	86	83	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	83	76	71	68	83	76	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174477
5°	169852
10°	147366
15°	113718
20°	79240
25°	41764
30°	11661
35°	5174
40°	2566
45°	1338
50°	573
55°	64
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859691

CATALOG NUMBER: LD4C08D010 EU4089040 4LBHYH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	23.0
10°-20°	244.4	45.1
20°-30°	141.3	26.0
30°-40°	24.8	4.6
40°-50°	6.3	1.2
50°-60°	0.7	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	510.6	94.1
0°-40°	535.4	98.7
0°-60°	542.4	100.0
0°-90°	542.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	542.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1420	
5°	1377	125
15°	894	244
25°	308	141
35°	34	25
45°	8	6
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859691

CATALOG NUMBER: LD4C08D010 EU4089040 4LBHYH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1420.2
2.5°	1417.8
5°	1377.3
7.5°	1292.6
10°	1181.3
12.5°	1050.9
15°	894.1
17.5°	732.5
20°	606.1
22.5°	455.2
25°	308.1
27.5°	176.2
30°	82.2
32.5°	56.2
35°	34.5
37.5°	23.0
40°	16.0
42.5°	11.0
45°	7.7
47.5°	5.0
50°	3.0
52.5°	1.4
55°	0.3
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)