

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859126

Luminaire Tested: **LD4C55D010 EU4559040 4LBMLI**

Issue Date: 7/19/2024



Test Information

Test Method: LM-79-08
Report Number: P859126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 7/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C55D010 EU4559040 4LBMLI
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5621.0 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859126

CATALOG NUMBER: LD4C55D010 EU4559040 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859126

CATALOG NUMBER: LD4C55D010 EU4559040 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1088629
5°	1070121
10°	983269
15°	823436
20°	659704
25°	530070
30°	394595
35°	225415
40°	105799
45°	44912
50°	14296
55°	7282
60°	5012
65°	3953
70°	2443
75°	0
80°	0
85°	0



TEST NUMBER: P859126

CATALOG NUMBER: LD4C55D010 EU4559040 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	802.3	14.3
10°-20°	1793.7	31.9
20°-30°	1783.3	31.7
30°-40°	971.2	17.3
40°-50°	224.5	4.0
50°-60°	31.6	0.6
60°-70°	11.7	0.2
70°-80°	2.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4379.3	77.9
0°-40°	5350.5	95.2
0°-60°	5606.6	99.7
0°-90°	5621.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5621.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8861	
5°	8677	802
15°	6474	1794
25°	3910	1783
35°	1503	971
45°	258	224
55°	34	32
65°	14	12
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P859126

CATALOG NUMBER: LD4C55D010 EU4559040 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8861.2
2.5°	8840.7
5°	8677.4
7.5°	8344.4
10°	7882.0
12.5°	7201.9
15°	6474.2
17.5°	5753.3
20°	5046.0
22.5°	4468.0
25°	3910.4
27.5°	3380.0
30°	2781.6
32.5°	2115.1
35°	1503.0
37.5°	1013.2
40°	659.7
42.5°	414.7
45°	258.5
47.5°	149.7
50°	74.8
52.5°	40.8
55°	34.0
57.5°	20.4
60°	20.4
62.5°	13.6
65°	13.6
67.5°	6.8
70°	6.8
72.5°	6.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)