

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859715

Luminaire Tested: **LD4C08D010 EU4089050 4LBMLI**

Issue Date: 7/19/2024



Test Information

Test Method: LM-79-08
Report Number: P859715
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 7/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08D010 EU4089050 4LBMLI
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 855.0 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859715

CATALOG NUMBER: LD4C08D010 EU4089050 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859715

CATALOG NUMBER: LD4C08D010 EU4089050 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	165594
5°	162774
10°	149561
15°	125254
20°	100341
25°	80627
30°	60021
35°	34285
40°	16085
45°	6828
50°	2179
55°	1114
60°	762
65°	610
70°	359
75°	0
80°	0
85°	0



TEST NUMBER: P859715

CATALOG NUMBER: LD4C08D010 EU4089050 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.0	14.3
10°-20°	272.8	31.9
20°-30°	271.3	31.7
30°-40°	147.7	17.3
40°-50°	34.1	4.0
50°-60°	4.8	0.6
60°-70°	1.8	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	666.1	77.9
0°-40°	813.8	95.2
0°-60°	852.8	99.7
0°-90°	855.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	855.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1348	
5°	1320	122
15°	985	273
25°	595	271
35°	229	148
45°	39	34
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859715

CATALOG NUMBER: LD4C08D010 EU4089050 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1347.9
2.5°	1344.7
5°	1319.9
7.5°	1269.2
10°	1198.9
12.5°	1095.5
15°	984.8
17.5°	875.1
20°	767.5
22.5°	679.6
25°	594.8
27.5°	514.1
30°	423.1
32.5°	321.7
35°	228.6
37.5°	154.1
40°	100.3
42.5°	63.1
45°	39.3
47.5°	22.8
50°	11.4
52.5°	6.2
55°	5.2
57.5°	3.1
60°	3.1
62.5°	2.1
65°	2.1
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)