

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859720

Luminaire Tested: **LX4C08D010 EX4C089050 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P859720
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089050 4LBMDLI
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 753.0 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859720

CATALOG NUMBER: LX4C08D010 EX4C089050 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P859720

CATALOG NUMBER: LX4C08D010 EX4C089050 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		66
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121502
5°	125641
10°	126919
15°	114329
20°	95007
25°	74541
30°	54545
35°	28196
40°	13391
45°	4708
50°	1070
55°	685
60°	491
65°	378
70°	251
75°	190
80°	141
85°	0



TEST NUMBER: P859720

CATALOG NUMBER: LX4C08D010 EX4C089050 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.3	12.9
10°-20°	247.6	32.9
20°-30°	250.5	33.3
30°-40°	127.7	17.0
40°-50°	25.0	3.3
50°-60°	3.0	0.4
60°-70°	1.3	0.2
70°-80°	0.5	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.4	79.1
0°-40°	723.2	96.0
0°-60°	751.2	99.8
0°-90°	753.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	753.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	989	
5°	1019	97
15°	899	248
25°	550	251
35°	188	128
45°	27	25
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859720

CATALOG NUMBER: LX4C08D010 EX4C089050 4LBMDLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	989.0
2.5°	998.2
5°	1018.8
7.5°	1030.7
10°	1017.4
12.5°	972.7
15°	898.9
17.5°	811.8
20°	726.7
22.5°	638.6
25°	549.9
27.5°	461.6
30°	384.5
32.5°	289.8
35°	188.0
37.5°	125.8
40°	83.5
42.5°	52.4
45°	27.1
47.5°	9.7
50°	5.6
52.5°	4.1
55°	3.2
57.5°	2.5
60°	2.0
62.5°	1.6
65°	1.3
67.5°	0.9
70°	0.7
72.5°	0.5
75°	0.4
77.5°	0.4
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)