

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859728

Luminaire Tested: **LX4C08D010 EX4C089050 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089050 4LBWH
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 762.0 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859728

CATALOG NUMBER: LX4C08D010 EX4C089050 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P859728

CATALOG NUMBER: LX4C08D010 EX4C089050 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60346
5°	60576
10°	60753
15°	60757
20°	60427
25°	59007
30°	55155
35°	47767
40°	37303
45°	26773
50°	17392
55°	10410
60°	6094
65°	3924
70°	2586
75°	1946
80°	1486
85°	0



TEST NUMBER: P859728

CATALOG NUMBER: LX4C08D010 EX4C089050 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	6.1
10°-20°	134.8	17.7
20°-30°	198.9	26.1
30°-40°	196.3	25.8
40°-50°	120.1	15.8
50°-60°	46.0	6.0
60°-70°	14.4	1.9
70°-80°	4.2	0.6
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.4	49.9
0°-40°	576.7	75.7
0°-60°	742.8	97.5
0°-90°	762.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	762.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	491	
5°	491	47
15°	478	135
25°	435	199
35°	318	196
45°	154	120
55°	49	46
65°	14	14
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P859728

CATALOG NUMBER: LX4C08D010 EX4C089050 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	491.2
2.5°	492.2
5°	491.2
7.5°	490.1
10°	487.0
12.5°	482.9
15°	477.7
17.5°	471.5
20°	462.2
22.5°	451.9
25°	435.3
27.5°	414.6
30°	388.8
32.5°	356.7
35°	318.5
37.5°	276.1
40°	232.6
42.5°	192.3
45°	154.1
47.5°	119.9
50°	91.0
52.5°	67.2
55°	48.6
57.5°	34.1
60°	24.8
62.5°	18.6
65°	13.5
67.5°	10.4
70°	7.2
72.5°	5.2
75°	4.1
77.5°	2.1
80°	2.1
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)