

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859462

Luminaire Tested: **LX4C70D010 EX4C709030 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P859462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C70D010 EX4C709030 4LBMLI
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6574.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859462

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859462

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2078398
5°	1870338
10°	1449929
15°	1049448
20°	726655
25°	529758
30°	384920
35°	227769
40°	95791
45°	29866
50°	3880
55°	2163
60°	2482
65°	2936
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859462

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1333.2	20.3
10°-20°	2282.5	34.7
20°-30°	1814.0	27.6
30°-40°	960.3	14.6
40°-50°	165.4	2.5
50°-60°	12.4	0.2
60°-70°	6.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5429.7	82.6
0°-40°	6390.0	97.2
0°-60°	6567.8	99.9
0°-90°	6574.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6574.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16918	
5°	15166	###
15°	8251	2282
25°	3908	1814
35°	1519	960
45°	172	165
55°	10	12
65°	10	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859462

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	16917.7
2.5°	16482.1
5°	15166.2
7.5°	13445.2
10°	11622.8
12.5°	9861.2
15°	8251.2
17.5°	6752.8
20°	5558.1
22.5°	4646.9
25°	3908.1
27.5°	3310.7
30°	2713.4
32.5°	2105.9
35°	1518.7
37.5°	1002.5
40°	597.3
42.5°	344.3
45°	171.9
47.5°	60.8
50°	20.3
52.5°	20.3
55°	10.1
57.5°	10.1
60°	10.1
62.5°	10.1
65°	10.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)