

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859741

Luminaire Tested: **LX4C08D010 EX4C089827 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P859741
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089827 4LBMLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 707.1 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859741

CATALOG NUMBER: LX4C08D010 EX4C089827 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859741

CATALOG NUMBER: LX4C08D010 EX4C089827 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	84	80	87	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	223569
5°	201189
10°	155961
15°	112891
20°	78168
25°	56987
30°	41409
35°	24506
40°	10312
45°	3214
50°	401
55°	236
60°	270
65°	320
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859741

CATALOG NUMBER: LX4C08D010 EX4C089827 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.4	20.3
10°-20°	245.5	34.7
20°-30°	195.1	27.6
30°-40°	103.3	14.6
40°-50°	17.8	2.5
50°-60°	1.3	0.2
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.1	82.6
0°-40°	687.4	97.2
0°-60°	706.5	99.9
0°-90°	707.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	707.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1820	
5°	1631	143
15°	888	246
25°	420	195
35°	163	103
45°	18	18
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859741

CATALOG NUMBER: LX4C08D010 EX4C089827 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1819.8
2.5°	1773.0
5°	1631.4
7.5°	1446.3
10°	1250.2
12.5°	1060.7
15°	887.6
17.5°	726.4
20°	597.9
22.5°	499.8
25°	420.4
27.5°	356.2
30°	291.9
32.5°	226.5
35°	163.4
37.5°	107.8
40°	64.3
42.5°	37.0
45°	18.5
47.5°	6.5
50°	2.1
52.5°	2.1
55°	1.1
57.5°	1.1
60°	1.1
62.5°	1.1
65°	1.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)