

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859822

Luminaire Tested: **LX4C08D010 EX4C089030 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P859822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089030 4LBSH
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND
4LBS TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 834.9 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 10.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859822

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P859822

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53650
5°	53399
10°	52295
15°	50392
20°	48072
25°	45478
30°	42898
35°	40404
40°	38025
45°	35461
50°	32319
55°	28551
60°	24178
65°	18953
70°	13506
75°	7452
80°	1273
85°	0



TEST NUMBER: P859822

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.9	4.9
10°-20°	111.2	13.3
20°-30°	154.4	18.5
30°-40°	168.5	20.2
40°-50°	157.2	18.8
50°-60°	119.3	14.3
60°-70°	65.3	7.8
70°-80°	17.9	2.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.5	36.7
0°-40°	474.9	56.9
0°-60°	751.4	90.0
0°-90°	834.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	834.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	437	
5°	433	41
15°	396	111
25°	336	154
35°	269	168
45°	204	157
55°	133	119
65°	65	65
75°	16	18
85°	0	0
90°	0	



TEST NUMBER: P859822

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	436.7
2.5°	436.7
5°	433.0
7.5°	427.5
10°	419.2
12.5°	408.2
15°	396.2
17.5°	381.6
20°	367.7
22.5°	351.1
25°	335.5
27.5°	319.9
30°	302.4
32.5°	285.9
35°	269.4
37.5°	252.8
40°	237.1
42.5°	220.6
45°	204.1
47.5°	187.6
50°	169.1
52.5°	151.8
55°	133.3
57.5°	115.9
60°	98.4
62.5°	80.9
65°	65.2
67.5°	50.6
70°	37.6
72.5°	25.7
75°	15.7
77.5°	7.3
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)