

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859652

Luminaire Tested: **LX4C08D010 EX4C089030 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089030 4LBMH
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 661.1 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859652

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P859652

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	67	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52348
5°	52548
10°	52706
15°	52706
20°	52413
25°	51185
30°	47849
35°	41423
40°	32363
45°	23229
50°	15080
55°	9039
60°	5283
65°	3401
70°	2263
75°	1709
80°	1273
85°	0



TEST NUMBER: P859652

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.6	6.1
10°-20°	116.9	17.7
20°-30°	172.5	26.1
30°-40°	170.3	25.8
40°-50°	104.2	15.8
50°-60°	39.9	6.0
60°-70°	12.5	1.9
70°-80°	3.7	0.6
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	330.0	49.9
0°-40°	500.3	75.7
0°-60°	644.4	97.5
0°-90°	661.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	661.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	426	
5°	426	41
15°	414	117
25°	378	173
35°	276	170
45°	134	104
55°	42	40
65°	12	13
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P859652

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	426.1
2.5°	427.0
5°	426.1
7.5°	425.2
10°	422.5
12.5°	418.9
15°	414.4
17.5°	409.0
20°	400.9
22.5°	392.0
25°	377.6
27.5°	359.7
30°	337.3
32.5°	309.5
35°	276.2
37.5°	239.5
40°	201.8
42.5°	166.8
45°	133.7
47.5°	104.0
50°	78.9
52.5°	58.3
55°	42.2
57.5°	29.6
60°	21.5
62.5°	16.2
65°	11.7
67.5°	9.0
70°	6.3
72.5°	4.5
75°	3.6
77.5°	1.8
80°	1.8
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)