

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859660

Luminaire Tested: **LX4C08D010 EX4C089030 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089030 4LBWLI
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 871.0 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859660

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBWLI

Luminous Intensity Polar Plot






TEST NUMBER: P859660

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBWL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P859660

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBWL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.2	6.0
10°-20°	164.7	18.9
20°-30°	256.9	29.5
30°-40°	250.0	28.7
40°-50°	124.8	14.3
50°-60°	19.3	2.2
60°-70°	2.3	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	473.8	54.4
0°-40°	723.8	83.1
0°-60°	868.0	99.7
0°-90°	871.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	871.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	534	
5°	541	52
15°	582	165
25°	565	257
35°	406	250
45°	157	125
55°	16	19
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P859660

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	533.7
2.5°	535.7
5°	540.6
7.5°	548.6
10°	558.6
12.5°	571.6
15°	581.6
17.5°	589.5
20°	590.5
22.5°	583.5
25°	564.6
27.5°	536.7
30°	501.7
32.5°	457.9
35°	406.0
37.5°	349.1
40°	289.3
42.5°	225.4
45°	156.6
47.5°	100.7
50°	60.8
52.5°	32.9
55°	16.0
57.5°	7.0
60°	4.0
62.5°	3.0
65°	2.0
67.5°	2.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)