

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859748

Luminaire Tested: **LX4C08D010 EX4C089827 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859748
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089827 4LBWLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 746.5 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859748

CATALOG NUMBER: LX4C08D010 EX4C089827 4LBWLI

Luminous Intensity Polar Plot




TEST NUMBER: P859748
CATALOG NUMBER: LX4C08D010 EX4C089827 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P859748

CATALOG NUMBER: LX4C08D010 EX4C089827 4LBWL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.7	6.0
10°-20°	141.1	18.9
20°-30°	220.2	29.5
30°-40°	214.2	28.7
40°-50°	107.0	14.3
50°-60°	16.6	2.2
60°-70°	2.0	0.3
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	406.1	54.4
0°-40°	620.3	83.1
0°-60°	743.9	99.7
0°-90°	746.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	746.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	457	
5°	463	45
15°	498	141
25°	484	220
35°	348	214
45°	134	107
55°	14	17
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P859748

CATALOG NUMBER: LX4C08D010 EX4C089827 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	457.3
2.5°	459.0
5°	463.3
7.5°	470.1
10°	478.7
12.5°	489.8
15°	498.4
17.5°	505.2
20°	506.1
22.5°	500.1
25°	483.9
27.5°	459.9
30°	430.0
32.5°	392.4
35°	347.9
37.5°	299.2
40°	247.9
42.5°	193.2
45°	134.2
47.5°	86.3
50°	52.2
52.5°	28.2
55°	13.7
57.5°	6.0
60°	3.4
62.5°	2.6
65°	1.7
67.5°	1.7
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)