

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859751

Luminaire Tested: **LX4C08D010 EX4C089830 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P859751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089830 4LBMDH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 557.4 lumens
Efficiency: N/A
Efficacy: 56.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859751

CATALOG NUMBER: LX4C08D010 EX4C089830 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P859751

CATALOG NUMBER: LX4C08D010 EX4C089830 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	63	60	68	63	59		67	62	59		66
9	76	66	60	56	74	65	60	56	64	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82484
5°	81381
10°	77556
15°	71772
20°	64598
25°	53666
30°	39011
35°	25286
40°	15300
45°	7888
50°	3574
55°	2163
60°	1450
65°	1047
70°	754
75°	522
80°	283
85°	282



TEST NUMBER: P859751

CATALOG NUMBER: LX4C08D010 EX4C089830 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.8	11.1
10°-20°	157.4	28.2
20°-30°	178.0	31.9
30°-40°	107.6	19.3
40°-50°	37.7	6.8
50°-60°	9.7	1.7
60°-70°	3.7	0.7
70°-80°	1.2	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	397.3	71.3
0°-40°	504.9	90.6
0°-60°	552.2	99.1
0°-90°	557.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	557.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	671	
5°	660	62
15°	564	157
25°	396	178
35°	169	108
45°	45	38
55°	10	10
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P859751

CATALOG NUMBER: LX4C08D010 EX4C089830 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	671.4
2.5°	668.6
5°	659.9
7.5°	644.3
10°	621.7
12.5°	594.5
15°	564.3
17.5°	531.0
20°	494.1
22.5°	448.9
25°	395.9
27.5°	335.3
30°	275.0
32.5°	217.4
35°	168.6
37.5°	127.9
40°	95.4
42.5°	68.6
45°	45.4
47.5°	27.9
50°	18.7
52.5°	13.5
55°	10.1
57.5°	7.8
60°	5.9
62.5°	4.6
65°	3.6
67.5°	2.8
70°	2.1
72.5°	1.5
75°	1.1
77.5°	0.8
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)