

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859766

Luminaire Tested: **LX4C08D010 EX4C089835 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089835 4LBMH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 598.3 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859766

CATALOG NUMBER: LX4C08D010 EX4C089835 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P859766

CATALOG NUMBER: LX4C08D010 EX4C089835 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47385
5°	47566
10°	47716
15°	47721
20°	47445
25°	46332
30°	43310
35°	37494
40°	29300
45°	21023
50°	13646
55°	8182
60°	4767
65°	3052
70°	2047
75°	1519
80°	1132
85°	0



TEST NUMBER: P859766

CATALOG NUMBER: LX4C08D010 EX4C089835 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.7	6.1
10°-20°	105.8	17.7
20°-30°	156.2	26.1
30°-40°	154.1	25.8
40°-50°	94.3	15.8
50°-60°	36.2	6.0
60°-70°	11.3	1.9
70°-80°	3.3	0.6
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	298.7	49.9
0°-40°	452.8	75.7
0°-60°	583.3	97.5
0°-90°	598.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	598.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	386	
5°	386	37
15°	375	106
25°	342	156
35°	250	154
45°	121	94
55°	38	36
65°	10	11
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P859766

CATALOG NUMBER: LX4C08D010 EX4C089835 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	385.7
2.5°	386.5
5°	385.7
7.5°	384.9
10°	382.5
12.5°	379.2
15°	375.2
17.5°	370.3
20°	362.9
22.5°	354.8
25°	341.8
27.5°	325.6
30°	305.3
32.5°	280.1
35°	250.0
37.5°	216.8
40°	182.7
42.5°	151.1
45°	121.0
47.5°	94.2
50°	71.4
52.5°	52.8
55°	38.2
57.5°	26.8
60°	19.4
62.5°	14.6
65°	10.5
67.5°	8.1
70°	5.7
72.5°	4.1
75°	3.2
77.5°	1.6
80°	1.6
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)