

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C15D010 EX4C159027 4LBSQH**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15D010 EX4C159027 4LBSQH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBSQ TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1183.0 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P#

CATALOG NUMBER: LD4C15D010 EX4C159027 4LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C15D010 EX4C159027 4LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113181
5°	111541
10°	106884
15°	100952
20°	94231
25°	85533
30°	71418
35°	51734
40°	32384
45°	18517
50°	9652
55°	5417
60°	3454
65°	2032
70°	1523
75°	671
80°	1000
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD4C15D010 EX4C159027 4LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.9	9.1
10°-20°	283.2	23.9
20°-30°	363.9	30.8
30°-40°	273.8	23.1
40°-50°	110.0	9.3
50°-60°	31.3	2.6
60°-70°	9.9	0.8
70°-80°	2.8	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	755.0	63.8
0°-40°	1028.8	87.0
0°-60°	1170.1	98.9
0°-90°	1183.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1183.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1173	
5°	1152	108
15°	1011	283
25°	803	364
35°	439	274
45°	136	110
55°	32	31
65°	9	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C15D010 EX4C159027 4LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1173.0
2.5°	1165.9
5°	1151.6
7.5°	1124.8
10°	1090.9
12.5°	1049.9
15°	1010.6
17.5°	965.9
20°	917.7
22.5°	866.0
25°	803.4
27.5°	728.4
30°	641.0
32.5°	542.7
35°	439.2
37.5°	342.8
40°	257.1
42.5°	189.3
45°	135.7
47.5°	92.9
50°	64.3
52.5°	44.7
55°	32.2
57.5°	23.2
60°	17.9
62.5°	12.5
65°	8.9
67.5°	7.1
70°	5.4
72.5°	3.6
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)