

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859820

Luminaire Tested: **LX4C08D010 EX4C089030 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859820
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089030 4LBNH
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBN TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 530.5 lumens
Efficiency: N/A
Efficacy: 49.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 10.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859820

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P859820

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	76	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81833
5°	80012
10°	73976
15°	66379
20°	58440
25°	50290
30°	40487
35°	26951
40°	14033
45°	6342
50°	2752
55°	1842
60°	1204
65°	814
70°	682
75°	475
80°	0
85°	0



TEST NUMBER: P859820

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.1	11.3
10°-20°	145.8	27.5
20°-30°	169.2	31.9
30°-40°	112.1	21.1
40°-50°	31.5	5.9
50°-60°	7.9	1.5
60°-70°	3.0	0.6
70°-80°	1.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	375.1	70.7
0°-40°	487.2	91.8
0°-60°	526.5	99.2
0°-90°	530.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	530.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	666	
5°	649	60
15°	522	146
25°	371	169
35°	180	112
45°	36	31
55°	9	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P859820

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	666.1
2.5°	663.2
5°	648.8
7.5°	623.7
10°	593.0
12.5°	558.4
15°	521.9
17.5°	486.3
20°	447.0
22.5°	410.4
25°	371.0
27.5°	333.4
30°	285.4
32.5°	234.6
35°	179.7
37.5°	128.8
40°	87.5
42.5°	56.8
45°	36.5
47.5°	22.2
50°	14.4
52.5°	10.6
55°	8.6
57.5°	6.7
60°	4.9
62.5°	3.9
65°	2.8
67.5°	1.9
70°	1.9
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)