

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563789

Luminaire Tested: **LD4C15D010 EX4C15D2W 4LBSQH**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P563789
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15D010 EX4C15D2W 4LBSQH
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBSQ TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1251.2 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563789

CATALOG NUMBER: LD4C15D010 EX4C15D2W 4LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P563789

CATALOG NUMBER: LD4C15D010 EX4C15D2W 4LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119704
5°	117963
10°	113037
15°	106765
20°	99652
25°	90473
30°	75540
35°	54726
40°	34248
45°	19581
50°	10222
55°	5720
60°	3647
65°	2169
70°	1608
75°	708
80°	1056
85°	0



TEST NUMBER: P563789

CATALOG NUMBER: LD4C15D010 EX4C15D2W 4LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.2	9.1
10°-20°	299.5	23.9
20°-30°	384.9	30.8
30°-40°	289.6	23.1
40°-50°	116.3	9.3
50°-60°	33.1	2.6
60°-70°	10.5	0.8
70°-80°	3.0	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	798.5	63.8
0°-40°	1088.1	87.0
0°-60°	1237.5	98.9
0°-90°	1251.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1251.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1241	
5°	1218	114
15°	1069	299
25°	850	385
35°	465	290
45°	144	116
55°	34	33
65°	10	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P563789

CATALOG NUMBER: LD4C15D010 EX4C15D2W 4LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1240.6
2.5°	1233.0
5°	1217.9
7.5°	1189.6
10°	1153.7
12.5°	1110.4
15°	1068.8
17.5°	1021.6
20°	970.5
22.5°	915.9
25°	849.8
27.5°	770.4
30°	678.0
32.5°	574.0
35°	464.6
37.5°	362.5
40°	271.9
42.5°	200.2
45°	143.5
47.5°	98.3
50°	68.1
52.5°	47.2
55°	34.0
57.5°	24.5
60°	18.9
62.5°	13.2
65°	9.5
67.5°	7.5
70°	5.7
72.5°	3.8
75°	1.9
77.5°	1.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)