

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859808

Luminaire Tested: **LX4C08D010 EX4C089030 4LBNLI**

Issue Date: 1/21/2022



Test Information

Test Method: LM-79-08
Report Number: P859808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C08D010 EX4C089030 4LBNLI
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBN TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 614.7 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 10.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859808

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P859808

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	91
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194330
5°	174872
10°	135564
15°	98125
20°	67931
25°	49531
30°	35975
35°	21297
40°	8965
45°	2797
50°	363
55°	214
60°	246
65°	291
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859808

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	20.3
10°-20°	213.4	34.7
20°-30°	169.6	27.6
30°-40°	89.8	14.6
40°-50°	15.5	2.5
50°-60°	1.2	0.2
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	507.6	82.6
0°-40°	597.4	97.2
0°-60°	614.1	99.9
0°-90°	614.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1582	
5°	1418	125
15°	772	213
25°	365	170
35°	142	90
45°	16	15
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859808

CATALOG NUMBER: LX4C08D010 EX4C089030 4LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1581.8
2.5°	1541.0
5°	1418.0
7.5°	1257.1
10°	1086.7
12.5°	922.0
15°	771.5
17.5°	631.4
20°	519.6
22.5°	434.4
25°	365.4
27.5°	309.5
30°	253.6
32.5°	196.9
35°	142.0
37.5°	93.8
40°	55.9
42.5°	32.2
45°	16.1
47.5°	5.7
50°	1.9
52.5°	1.9
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)