

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563780

Luminaire Tested: **LD4C10D010 EX4C10D2W 4LBSQH**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P563780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10D010 EX4C10D2W 4LBSQH
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBSQ TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 816.7 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563780

CATALOG NUMBER: LD4C10D010 EX4C10D2W 4LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P563780

CATALOG NUMBER: LD4C10D010 EX4C10D2W 4LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78146
5°	77011
10°	73797
15°	69695
20°	65059
25°	59066
30°	49313
35°	35714
40°	22357
45°	12786
50°	6650
55°	3735
60°	2374
65°	1416
70°	1044
75°	447
80°	667
85°	0



TEST NUMBER: P563780

CATALOG NUMBER: LD4C10D010 EX4C10D2W 4LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	9.1
10°-20°	195.5	23.9
20°-30°	251.3	30.8
30°-40°	189.0	23.1
40°-50°	75.9	9.3
50°-60°	21.6	2.6
60°-70°	6.8	0.8
70°-80°	1.9	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	521.3	63.8
0°-40°	710.3	87.0
0°-60°	807.8	98.9
0°-90°	816.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	816.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	810	
5°	795	75
15°	698	196
25°	555	251
35°	303	189
45°	94	76
55°	22	22
65°	6	7
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P563780

CATALOG NUMBER: LD4C10D010 EX4C10D2W 4LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	809.9
2.5°	805.0
5°	795.1
7.5°	776.6
10°	753.2
12.5°	724.9
15°	697.7
17.5°	666.9
20°	633.6
22.5°	597.9
25°	554.8
27.5°	502.9
30°	442.6
32.5°	374.7
35°	303.2
37.5°	236.7
40°	177.5
42.5°	130.7
45°	93.7
47.5°	64.1
50°	44.3
52.5°	30.8
55°	22.2
57.5°	16.1
60°	12.3
62.5°	8.6
65°	6.2
67.5°	4.9
70°	3.7
72.5°	2.4
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)