

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C55D010 EX4C559040 4LBSQH**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C55D010 EX4C559040 4LBSQH
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBSQ TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4770.0 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P#

CATALOG NUMBER: LD4C55D010 EX4C559040 4LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C55D010 EX4C559040 4LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	456373
5°	449738
10°	430954
15°	407033
20°	379941
25°	344900
30°	287954
35°	208608
40°	130593
45°	74641
50°	38924
55°	21802
60°	13894
65°	8219
70°	6094
75°	2684
80°	4001
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD4C55D010 EX4C559040 4LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	435.2	9.1
10°-20°	1141.8	23.9
20°-30°	1467.3	30.8
30°-40°	1104.0	23.1
40°-50°	443.4	9.3
50°-60°	126.0	2.6
60°-70°	39.9	0.8
70°-80°	11.4	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3044.3	63.8
0°-40°	4148.3	87.0
0°-60°	4717.7	98.9
0°-90°	4770.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4770.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4730	
5°	4643	435
15°	4075	1142
25°	3240	1467
35°	1771	1104
45°	547	443
55°	130	126
65°	36	40
75°	7	11
85°	0	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C55D010 EX4C559040 4LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4729.8
2.5°	4700.9
5°	4643.3
7.5°	4535.3
10°	4398.5
12.5°	4233.1
15°	4074.7
17.5°	3894.6
20°	3700.2
22.5°	3491.7
25°	3239.6
27.5°	2937.1
30°	2584.5
32.5°	2188.4
35°	1771.0
37.5°	1382.1
40°	1036.8
42.5°	763.1
45°	547.0
47.5°	374.5
50°	259.3
52.5°	180.1
55°	129.6
57.5°	93.6
60°	72.0
62.5°	50.4
65°	36.0
67.5°	28.8
70°	21.6
72.5°	14.4
75°	7.2
77.5°	7.2
80°	7.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)