

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C50D010 EX4C509040 4LBSQH**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C50D010 EX4C509040 4LBSQH
Description: 4 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBSQ TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4267.0 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P#

CATALOG NUMBER: LD4C50D010 EX4C509040 4LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C50D010 EX4C509040 4LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	408245
5°	402317
10°	385502
15°	364109
20°	339875
25°	308532
30°	257593
35°	186617
40°	116813
45°	66768
50°	34811
55°	19514
60°	12428
65°	7352
70°	5445
75°	2386
80°	3556
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD4C50D010 EX4C509040 4LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	389.3	9.1
10°-20°	1021.4	23.9
20°-30°	1312.6	30.8
30°-40°	987.6	23.1
40°-50°	396.6	9.3
50°-60°	112.8	2.6
60°-70°	35.7	0.8
70°-80°	10.1	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2723.3	63.8
0°-40°	3710.9	87.0
0°-60°	4220.3	98.9
0°-90°	4267.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4267.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4231	
5°	4154	389
15°	3645	1021
25°	2898	1313
35°	1584	988
45°	489	397
55°	116	113
65°	32	36
75°	6	10
85°	0	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C50D010 EX4C509040 4LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4231.0
2.5°	4205.2
5°	4153.7
7.5°	4057.0
10°	3934.6
12.5°	3786.8
15°	3645.0
17.5°	3484.0
20°	3310.0
22.5°	3123.5
25°	2898.0
27.5°	2627.4
30°	2312.0
32.5°	1957.7
35°	1584.3
37.5°	1236.4
40°	927.4
42.5°	682.6
45°	489.3
47.5°	335.0
50°	231.9
52.5°	161.1
55°	116.0
57.5°	83.8
60°	64.4
62.5°	45.1
65°	32.2
67.5°	25.8
70°	19.3
72.5°	12.9
75°	6.4
77.5°	6.4
80°	6.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)