

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778799

Luminaire Tested: LER4D02D010-EC4DR650210IC9040-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P778799
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D02D010-EC4DR650210IC9040-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 331.3 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778799

CATALOG NUMBER: LER4D02D010-EC4DR650210IC9040-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P778799

CATALOG NUMBER: LER4D02D010-EC4DR650210IC9040-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	89		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17574
5°	17529
10°	17513
15°	16972
20°	15451
25°	13468
30°	11202
35°	8869
40°	6404
45°	4047
50°	2108
55°	1120
60°	584
65°	318
70°	137
75°	158
80°	101
85°	67

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4047 cd/sqm



TEST NUMBER: P778799

CATALOG NUMBER: LER4D02D010-EC4DR650210IC9040-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.5	8.6
10°-20°	77.9	23.5
20°-30°	95.3	28.7
30°-40°	77.3	23.3
40°-50°	38.5	11.6
50°-60°	10.7	3.2
60°-70°	2.4	0.7
70°-80°	0.6	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	201.6	60.9
0°-40°	278.9	84.2
0°-60°	328.1	99.0
0°-90°	331.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	331.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	301	
5°	299	28
15°	281	78
25°	209	95
35°	124	77
45°	49	38
55°	11	11
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P778799

CATALOG NUMBER: LER4D02D010-EC4DR650210IC9040-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	300.9
2.5°	300.7
5°	299.0
7.5°	298.0
10°	295.3
12.5°	289.9
15°	280.7
17.5°	266.5
20°	248.6
22.5°	229.4
25°	209.0
27.5°	187.2
30°	166.1
32.5°	145.2
35°	124.4
37.5°	103.7
40°	84.0
42.5°	65.5
45°	49.0
47.5°	34.1
50°	23.2
52.5°	16.0
55°	11.0
57.5°	7.4
60°	5.0
62.5°	3.5
65°	2.3
67.5°	1.2
70°	0.8
72.5°	0.7
75°	0.7
77.5°	0.5
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)