

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563870

Luminaire Tested: **LD4C55D010 EX4C559030 4LBSQH**

Issue Date: 2/9/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P563870  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/9/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C55D010 EX4C559030 4LBSQH  
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBSQ TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4697.0 lumens  
Efficiency: N/A  
Efficacy: 73.5 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 63.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563870

CATALOG NUMBER: LD4C55D010 EX4C559030 4LBSQH

### Luminous Intensity Polar Plot





TEST NUMBER: P563870

CATALOG NUMBER: LD4C55D010 EX4C559030 4LBSQH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  |
| 3   | 101 | 94  | 89  | 85  | 99  | 93  | 88  | 84  | 90  | 86  | 83  |  | 88  | 84  | 82  |  | 86  |
| 4   | 96  | 88  | 82  | 77  | 94  | 86  | 81  | 77  | 84  | 80  | 76  |  | 82  | 78  | 75  |  | 80  |
| 5   | 90  | 82  | 75  | 71  | 89  | 81  | 75  | 70  | 79  | 74  | 70  |  | 77  | 73  | 69  |  | 75  |
| 6   | 86  | 76  | 70  | 65  | 84  | 75  | 69  | 65  | 74  | 68  | 64  |  | 72  | 68  | 64  |  | 71  |
| 7   | 81  | 71  | 65  | 60  | 80  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 59  |  | 67  |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 59  | 56  |  | 64  | 59  | 55  |  | 63  |
| 9   | 73  | 63  | 56  | 52  | 72  | 62  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 52  |  | 59  |
| 10  | 69  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 52  | 49  |  | 57  | 52  | 48  |  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 449387 |
| 5°  | 442861 |
| 10° | 424350 |
| 15° | 400799 |
| 20° | 374130 |
| 25° | 339619 |
| 30° | 283553 |
| 35° | 205416 |
| 40° | 128590 |
| 45° | 73509  |
| 50° | 38323  |
| 55° | 21482  |
| 60° | 13682  |
| 65° | 8105   |
| 70° | 6009   |
| 75° | 2647   |
| 80° | 3945   |
| 85° | 0      |



TEST NUMBER: P563870

CATALOG NUMBER: LD4C55D010 EX4C559030 4LBSQH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 428.5  | 9.1       |
| 10°-20°   | 1124.3 | 23.9      |
| 20°-30°   | 1444.9 | 30.8      |
| 30°-40°   | 1087.1 | 23.1      |
| 40°-50°   | 436.6  | 9.3       |
| 50°-60°   | 124.1  | 2.6       |
| 60°-70°   | 39.3   | 0.8       |
| 70°-80°   | 11.2   | 0.2       |
| 80°-90°   | 1.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2997.7 | 63.8      |
| 0°-40°    | 4084.8 | 87.0      |
| 0°-60°    | 4645.6 | 98.9      |
| 0°-90°    | 4697.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4697.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 4657 |      |
| 5°  | 4572 | 429  |
| 15° | 4012 | 1124 |
| 25° | 3190 | 1445 |
| 35° | 1744 | 1087 |
| 45° | 539  | 437  |
| 55° | 128  | 124  |
| 65° | 36   | 39   |
| 75° | 7    | 11   |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P563870

CATALOG NUMBER: LD4C55D010 EX4C559030 4LBSQH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 4657.4 |
| 2.5°  | 4629.0 |
| 5°    | 4572.3 |
| 7.5°  | 4465.9 |
| 10°   | 4331.1 |
| 12.5° | 4168.4 |
| 15°   | 4012.3 |
| 17.5° | 3835.0 |
| 20°   | 3643.6 |
| 22.5° | 3438.2 |
| 25°   | 3190.0 |
| 27.5° | 2892.2 |
| 30°   | 2545.0 |
| 32.5° | 2154.9 |
| 35°   | 1743.9 |
| 37.5° | 1361.0 |
| 40°   | 1020.9 |
| 42.5° | 751.4  |
| 45°   | 538.7  |
| 47.5° | 368.8  |
| 50°   | 255.3  |
| 52.5° | 177.3  |
| 55°   | 127.7  |
| 57.5° | 92.2   |
| 60°   | 70.9   |
| 62.5° | 49.6   |
| 65°   | 35.5   |
| 67.5° | 28.4   |
| 70°   | 21.3   |
| 72.5° | 14.2   |
| 75°   | 7.1    |
| 77.5° | 7.1    |
| 80°   | 7.1    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)