

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778928

Luminaire Tested: LER4D05D010-EC4DR300210IC9027-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P778928
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D05D010-EC4DR300210IC9027-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 593.1 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778928

CATALOG NUMBER: LER4D05D010-EC4DR300210IC9027-4LBS1B

Luminous Intensity Polar Plot



TEST NUMBER: P778928

CATALOG NUMBER: LER4D05D010-EC4DR300210IC9027-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	145968	145968	145968
5°	141777	141616	141785
10°	122804	121934	122773
15°	80123	79687	79291
20°	39840	41339	39783
25°	20067	22634	19653
30°	8034	8759	7000
35°	3728	3569	2990
40°	1609	1789	1519
45°	1137	1407	1147
50°	393	1024	405
55°	227	427	240
60°	153	184	153
65°	109	109	109
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 1407 cd/sqm



TEST NUMBER: P778928

CATALOG NUMBER: LER4D05D010-EC4DR300210IC9027-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.7	28.3
10°-20°	270.1	45.5
20°-30°	116.7	19.7
30°-40°	26.6	4.5
40°-50°	9.1	1.5
50°-60°	2.2	0.4
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.5	93.5
0°-40°	581.1	98.0
0°-60°	592.4	99.9
0°-90°	593.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	593.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1907	1907	1907	1907	1907	
5°	1845	1843	1843	1847	1845	168
15°	1011	999	1006	1002	1001	271
25°	238	247	268	240	233	114
35°	40	41	38	38	32	27
45°	10	13	13	13	11	7
55°	2	2	3	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P778928

CATALOG NUMBER: LER4D05D010-EC4DR300210IC9027-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1907.0	1907.0	1907.0	1907.0	1907.0
2.5°	1894.3	1893.0	1893.8	1894.7	1895.1
5°	1845.2	1843.4	1843.1	1846.9	1845.3
7.5°	1746.1	1743.5	1739.7	1748.4	1756.6
10°	1580.0	1577.2	1568.8	1572.9	1579.6
12.5°	1334.7	1325.7	1325.5	1338.6	1336.8
15°	1011.1	998.9	1005.6	1002.4	1000.6
17.5°	679.9	675.2	684.2	681.5	669.8
20°	489.1	490.3	507.5	498.9	488.4
22.5°	356.9	361.3	381.6	359.4	351.3
25°	237.6	246.6	268.0	240.4	232.7
27.5°	146.2	150.3	171.9	144.3	140.1
30°	90.9	88.9	99.1	85.0	79.2
32.5°	59.6	57.0	60.3	54.1	49.4
35°	39.9	40.7	38.2	37.9	32.0
37.5°	24.9	28.6	25.3	27.0	20.6
40°	16.1	20.8	17.9	19.8	15.2
42.5°	13.2	16.0	14.7	15.6	13.5
45°	10.5	13.0	13.0	13.0	10.6
47.5°	5.8	8.7	11.1	8.9	6.2
50°	3.3	4.4	8.6	4.6	3.4
52.5°	2.2	2.5	5.9	2.6	2.3
55°	1.7	1.8	3.2	1.9	1.8
57.5°	1.3	1.4	1.7	1.4	1.3
60°	1.0	1.0	1.2	1.1	1.0
62.5°	0.7	0.7	0.9	0.7	0.7
65°	0.6	0.6	0.6	0.6	0.6
67.5°	0.3	0.4	0.4	0.4	0.4
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)