

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779076

Luminaire Tested: LER4D05D010-EC4DR600210IC9030-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D05D010-EC4DR600210IC9030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 628.5 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779076

CATALOG NUMBER: LER4D05D010-EC4DR600210IC9030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P779076

CATALOG NUMBER: LER4D05D010-EC4DR600210IC9030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68725
5°	68549
10°	70828
15°	70912
20°	65241
25°	55492
30°	42277
35°	29904
40°	17558
45°	7077
50°	2363
55°	1143
60°	459
65°	78
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7077 cd/sqm



TEST NUMBER: P779076

CATALOG NUMBER: LER4D05D010-EC4DR600210IC9030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	9.6
10°-20°	173.7	27.6
20°-30°	207.8	33.1
30°-40°	139.0	22.1
40°-50°	41.2	6.6
50°-60°	5.9	0.9
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.8	70.3
0°-40°	580.8	92.4
0°-60°	627.9	99.9
0°-90°	628.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	628.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	629	
5°	625	60
15°	627	174
25°	460	208
35°	224	139
45°	46	41
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779076

CATALOG NUMBER: LER4D05D010-EC4DR600210IC9030-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	629.0
2.5°	628.2
5°	625.0
7.5°	633.5
10°	638.4
12.5°	637.5
15°	626.9
17.5°	601.6
20°	561.1
22.5°	512.5
25°	460.3
27.5°	401.5
30°	335.1
32.5°	275.9
35°	224.2
37.5°	172.3
40°	123.1
42.5°	81.2
45°	45.8
47.5°	23.4
50°	13.9
52.5°	9.0
55°	6.0
57.5°	3.8
60°	2.1
62.5°	0.9
65°	0.3
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)