

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779097

Luminaire Tested: LER4D05D010-EC4DR650210IC9027-4LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P779097  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER4D05D010-EC4DR650210IC9027-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 567.6 lumens  
Efficiency: N/A  
Efficacy: 75.7 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P779097

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9027-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P779097

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9027-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |  |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0 |  |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |  |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |  |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |  |  |  |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 95  | 94  | 93  |    |    |   |  |  |  |
| 2   | 107 | 102 | 97  | 94  | 105 | 100 | 96  | 92  | 97  | 93  | 90  | 94  | 91  | 88  | 91  | 89  | 87  | 85  |    |    |   |  |  |  |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 86  | 82  | 87  | 84  | 81  | 85  | 82  | 80  | 78  |    |    |   |  |  |  |
| 4   | 95  | 87  | 81  | 76  | 93  | 86  | 80  | 76  | 84  | 79  | 75  | 82  | 77  | 74  | 80  | 76  | 73  | 72  |    |    |   |  |  |  |
| 5   | 90  | 81  | 74  | 70  | 88  | 80  | 74  | 69  | 78  | 73  | 69  | 76  | 72  | 68  | 75  | 71  | 68  | 66  |    |    |   |  |  |  |
| 6   | 85  | 75  | 69  | 64  | 83  | 74  | 68  | 64  | 73  | 67  | 63  | 71  | 67  | 63  | 70  | 66  | 62  | 61  |    |    |   |  |  |  |
| 7   | 80  | 70  | 64  | 59  | 79  | 69  | 63  | 59  | 68  | 63  | 59  | 67  | 62  | 58  | 66  | 61  | 58  | 56  |    |    |   |  |  |  |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 54  | 63  | 58  | 54  | 62  | 57  | 54  | 52  |    |    |   |  |  |  |
| 9   | 72  | 61  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 54  | 51  | 59  | 54  | 50  | 58  | 54  | 50  | 49  |    |    |   |  |  |  |
| 10  | 68  | 58  | 52  | 47  | 67  | 57  | 51  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 55  | 50  | 47  | 46  |    |    |   |  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    |
|-----|-------|
| 0°  | 30101 |
| 5°  | 30023 |
| 10° | 29996 |
| 15° | 29071 |
| 20° | 26464 |
| 25° | 23064 |
| 30° | 19186 |
| 35° | 15201 |
| 40° | 10971 |
| 45° | 6930  |
| 50° | 3616  |
| 55° | 1924  |
| 60° | 1016  |
| 65° | 553   |
| 70° | 239   |
| 75° | 248   |
| 80° | 168   |
| 85° | 134   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle:  $0^\circ$ 

Vertical Angle:  $45^\circ$

Luminance: 6930 cd/sqm



TEST NUMBER: P779097

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9027-4LBS1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 48.7   | 8.6       |
| 10°-20°   | 133.5  | 23.5      |
| 20°-30°   | 163.1  | 28.7      |
| 30°-40°   | 132.4  | 23.3      |
| 40°-50°   | 65.9   | 11.6      |
| 50°-60°   | 18.4   | 3.2       |
| 60°-70°   | 4.2    | 0.7       |
| 70°-80°   | 1.1    | 0.2       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 345.3  | 60.8      |
| 0°-40°    | 477.7  | 84.2      |
| 0°-60°    | 562.0  | 99.0      |
| 0°-90°    | 567.6  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 567.6  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 515 |      |
| 5°  | 512 | 49   |
| 15° | 481 | 133  |
| 25° | 358 | 163  |
| 35° | 213 | 132  |
| 45° | 84  | 66   |
| 55° | 19  | 18   |
| 65° | 4   | 4    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P779097

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9027-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 515.4 |
| 2.5°  | 515.0 |
| 5°    | 512.1 |
| 7.5°  | 510.4 |
| 10°   | 505.8 |
| 12.5° | 496.4 |
| 15°   | 480.8 |
| 17.5° | 456.4 |
| 20°   | 425.8 |
| 22.5° | 392.8 |
| 25°   | 357.9 |
| 27.5° | 320.6 |
| 30°   | 284.5 |
| 32.5° | 248.8 |
| 35°   | 213.2 |
| 37.5° | 177.7 |
| 40°   | 143.9 |
| 42.5° | 112.2 |
| 45°   | 83.9  |
| 47.5° | 58.4  |
| 50°   | 39.8  |
| 52.5° | 27.4  |
| 55°   | 18.9  |
| 57.5° | 12.7  |
| 60°   | 8.7   |
| 62.5° | 6.0   |
| 65°   | 4.0   |
| 67.5° | 2.1   |
| 70°   | 1.4   |
| 72.5° | 1.3   |
| 75°   | 1.1   |
| 77.5° | 0.7   |
| 80°   | 0.5   |
| 82.5° | 0.4   |
| 85°   | 0.2   |
| 87.5° | 0.2   |
| 90°   | 0.0   |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)