

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779102

Luminaire Tested: LER4D05D010-EC4DR650210IC9030-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P779102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D05D010-EC4DR650210IC9030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 615.4 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779102

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P779102

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32630
5°	32550
10°	32523
15°	31520
20°	28696
25°	25010
30°	20798
35°	16477
40°	11894
45°	7516
50°	3916
55°	2087
60°	1086
65°	608
70°	256
75°	271
80°	202
85°	134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7516 cd/sqm



TEST NUMBER: P779102

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.8	8.6
10°-20°	144.7	23.5
20°-30°	176.9	28.7
30°-40°	143.5	23.3
40°-50°	71.5	11.6
50°-60°	19.9	3.2
60°-70°	4.5	0.7
70°-80°	1.2	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	374.4	60.8
0°-40°	517.9	84.2
0°-60°	609.4	99.0
0°-90°	615.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	559	
5°	555	53
15°	521	145
25°	388	177
35°	231	143
45°	91	72
55°	20	20
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P779102

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	558.7
2.5°	558.3
5°	555.2
7.5°	553.4
10°	548.4
12.5°	538.2
15°	521.3
17.5°	494.9
20°	461.7
22.5°	425.9
25°	388.1
27.5°	347.6
30°	308.4
32.5°	269.7
35°	231.1
37.5°	192.6
40°	156.0
42.5°	121.7
45°	91.0
47.5°	63.4
50°	43.1
52.5°	29.7
55°	20.5
57.5°	13.8
60°	9.3
62.5°	6.5
65°	4.4
67.5°	2.2
70°	1.5
72.5°	1.4
75°	1.2
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)