

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779107

Luminaire Tested: LER4D05D010-EC4DR650210IC9035-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P779107
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D05D010-EC4DR650210IC9035-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 587.9 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779107

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9035-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P779107

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9035-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31176
5°	31096
10°	31070
15°	30111
20°	27415
25°	23888
30°	19868
35°	15743
40°	11360
45°	7178
50°	3743
55°	1986
60°	1040
65°	580
70°	239
75°	271
80°	202
85°	134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7178 cd/sqm



TEST NUMBER: P779107

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9035-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.5	8.6
10°-20°	138.2	23.5
20°-30°	169.0	28.7
30°-40°	137.1	23.3
40°-50°	68.3	11.6
50°-60°	19.1	3.2
60°-70°	4.3	0.7
70°-80°	1.1	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	357.7	60.8
0°-40°	494.8	84.2
0°-60°	582.1	99.0
0°-90°	587.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	534	
5°	530	50
15°	498	138
25°	371	169
35°	221	137
45°	87	68
55°	20	19
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P779107

CATALOG NUMBER: LER4D05D010-EC4DR650210IC9035-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	533.8
2.5°	533.4
5°	530.4
7.5°	528.7
10°	523.9
12.5°	514.2
15°	498.0
17.5°	472.8
20°	441.1
22.5°	406.9
25°	370.7
27.5°	332.0
30°	294.6
32.5°	257.7
35°	220.8
37.5°	184.0
40°	149.0
42.5°	116.3
45°	86.9
47.5°	60.6
50°	41.2
52.5°	28.4
55°	19.5
57.5°	13.2
60°	8.9
62.5°	6.2
65°	4.2
67.5°	2.1
70°	1.4
72.5°	1.3
75°	1.2
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)