

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779218

Luminaire Tested: LER4D08D010-EC4DR250210IC9027-4LBS1LI

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P779218  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER4D08D010-EC4DR250210IC9027-4LBS1LI  
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 715.0 lumens  
Efficiency: N/A  
Efficacy: 80.3 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P779218

CATALOG NUMBER: LER4D08D010-EC4DR250210IC9027-4LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P779218

CATALOG NUMBER: LER4D08D010-EC4DR250210IC9027-4LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 |  | 103 | 102 | 101 |  | 99  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98  |  | 99  | 97  | 96  |  | 97  |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 93  |  | 96  | 93  | 91  |  | 94  |
| 4   | 103 | 97  | 93  | 90  | 102 | 96  | 93  | 90  | 94  | 91  | 89  |  | 93  | 90  | 88  |  | 91  |
| 5   | 100 | 93  | 89  | 86  | 98  | 93  | 89  | 86  | 91  | 87  | 85  |  | 89  | 86  | 84  |  | 88  |
| 6   | 97  | 90  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 81  |  | 87  | 83  | 81  |  | 85  |
| 7   | 93  | 87  | 82  | 79  | 92  | 86  | 82  | 79  | 85  | 81  | 78  |  | 84  | 80  | 78  |  | 83  |
| 8   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 78  | 76  |  | 81  | 78  | 75  |  | 80  |
| 9   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 80  | 76  | 73  |  | 79  | 75  | 73  |  | 78  |
| 10  | 85  | 78  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  |  | 76  | 73  | 71  |  | 76  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 296282 |
| 5°  | 275950 |
| 10° | 196841 |
| 15° | 115932 |
| 20° | 72136  |
| 25° | 39591  |
| 30° | 18104  |
| 35° | 6856   |
| 40° | 3109   |
| 45° | 1870   |
| 50° | 782    |
| 55° | 495    |
| 60° | 350    |
| 65° | 233    |
| 70° | 32     |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1870 cd/sqm



TEST NUMBER: P779218

CATALOG NUMBER: LER4D08D010-EC4DR250210IC9027-4LBS1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 216.2  | 30.2      |
| 10°-20°   | 292.9  | 41.0      |
| 20°-30°   | 155.0  | 21.7      |
| 30°-40°   | 38.3   | 5.4       |
| 40°-50°   | 9.3    | 1.3       |
| 50°-60°   | 2.5    | 0.3       |
| 60°-70°   | 0.8    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 664.1  | 92.9      |
| 0°-40°    | 702.3  | 98.2      |
| 0°-60°    | 714.1  | 99.9      |
| 0°-90°    | 715.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 715.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2712 |      |
| 5°  | 2516 | 216  |
| 15° | 1025 | 293  |
| 25° | 328  | 155  |
| 35° | 51   | 38   |
| 45° | 12   | 9    |
| 55° | 3    | 2    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P779218

CATALOG NUMBER: LER4D08D010-EC4DR250210IC9027-4LBS1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2711.7 |
| 2.5°  | 2667.1 |
| 5°    | 2516.0 |
| 7.5°  | 2212.3 |
| 10°   | 1774.2 |
| 12.5° | 1341.2 |
| 15°   | 1024.9 |
| 17.5° | 798.8  |
| 20°   | 620.4  |
| 22.5° | 465.2  |
| 25°   | 328.4  |
| 27.5° | 220.2  |
| 30°   | 143.5  |
| 32.5° | 87.3   |
| 35°   | 51.4   |
| 37.5° | 31.5   |
| 40°   | 21.8   |
| 42.5° | 16.6   |
| 45°   | 12.1   |
| 47.5° | 7.3    |
| 50°   | 4.6    |
| 52.5° | 3.3    |
| 55°   | 2.6    |
| 57.5° | 2.1    |
| 60°   | 1.6    |
| 62.5° | 1.3    |
| 65°   | 0.9    |
| 67.5° | 0.3    |
| 70°   | 0.1    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9







— 0°-180°







(END OF REPORT)