

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779247

Luminaire Tested: LER4D08D010-EC4DR300210IC9030-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D08D010-EC4DR300210IC9030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 730.4 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779247

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9030-4LBS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P779247

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	179770	179770	179770
5°	174617	174410	174625
10°	151244	150171	151205
15°	98682	98143	97652
20°	49069	50910	49004
25°	24720	27871	24205
30°	9899	10783	8626
35°	4588	4392	3682
40°	1978	2198	1869
45°	1396	1732	1407
50°	476	1262	500
55°	280	520	294
60°	199	230	199
65°	127	127	127
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 1732 cd/sqm



TEST NUMBER: P779247

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.5	28.3
10°-20°	332.6	45.5
20°-30°	143.7	19.7
30°-40°	32.8	4.5
40°-50°	11.2	1.5
50°-60°	2.7	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.9	93.5
0°-40°	715.6	98.0
0°-60°	729.6	99.9
0°-90°	730.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	730.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2349	2349	2349	2349	2349	
5°	2273	2270	2270	2275	2273	207
15°	1245	1230	1238	1234	1232	333
25°	293	304	330	296	287	140
35°	49	50	47	47	39	33
45°	13	16	16	16	13	9
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P779247

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2348.6	2348.6	2348.6	2348.6	2348.6
2.5°	2333.1	2331.5	2332.4	2333.5	2334.0
5°	2272.6	2270.3	2269.9	2274.6	2272.7
7.5°	2150.4	2147.3	2142.5	2153.3	2163.3
10°	1945.9	1942.4	1932.1	1937.2	1945.4
12.5°	1643.9	1632.7	1632.5	1648.6	1646.4
15°	1245.3	1230.2	1238.5	1234.5	1232.3
17.5°	837.4	831.6	842.7	839.3	824.9
20°	602.4	603.9	625.0	614.4	601.6
22.5°	439.6	445.0	470.0	442.7	432.6
25°	292.7	303.7	330.0	296.0	286.6
27.5°	180.0	185.1	211.7	177.7	172.6
30°	112.0	109.4	122.0	104.7	97.6
32.5°	73.5	70.2	74.3	66.6	60.9
35°	49.1	50.1	47.0	46.7	39.4
37.5°	30.7	35.3	31.1	33.2	25.4
40°	19.8	25.6	22.0	24.4	18.7
42.5°	16.3	19.7	18.1	19.3	16.6
45°	12.9	16.0	16.0	16.0	13.0
47.5°	7.2	10.7	13.7	10.9	7.6
50°	4.0	5.4	10.6	5.7	4.2
52.5°	2.8	3.1	7.3	3.2	2.9
55°	2.1	2.2	3.9	2.3	2.2
57.5°	1.6	1.7	2.1	1.7	1.6
60°	1.3	1.3	1.5	1.4	1.3
62.5°	0.9	0.9	1.0	0.9	0.9
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.3	0.5	0.5	0.5	0.5
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)