

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779252

Luminaire Tested: LER4D08D010-EC4DR300210IC9040-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D08D010-EC4DR300210IC9040-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 781.5 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779252

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9040-4LBS1B

Luminous Intensity Polar Plot



TEST NUMBER: P779252

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9040-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	192369	192369	192369
5°	186842	186626	186857
10°	161837	160695	161798
15°	105592	105021	104491
20°	52506	54469	52433
25°	26452	29822	25911
30°	10588	11534	9227
35°	4906	4709	3943
40°	2118	2348	1998
45°	1494	1851	1505
50°	512	1346	548
55°	294	560	307
60°	214	245	214
65°	127	127	127
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 1851 cd/sqm



TEST NUMBER: P779252

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9040-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.0	28.3
10°-20°	355.9	45.5
20°-30°	153.8	19.7
30°-40°	35.1	4.5
40°-50°	12.0	1.5
50°-60°	2.9	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.7	93.5
0°-40°	765.8	98.0
0°-60°	780.7	99.9
0°-90°	781.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	781.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2513	2513	2513	2513	2513	
5°	2432	2429	2429	2434	2432	221
15°	1332	1316	1325	1321	1319	357
25°	313	325	353	317	307	150
35°	52	54	50	50	42	36
45°	14	17	17	17	14	10
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P779252

CATALOG NUMBER: LER4D08D010-EC4DR300210IC9040-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2513.2	2513.2	2513.2	2513.2	2513.2
2.5°	2496.5	2494.8	2495.8	2497.0	2497.5
5°	2431.7	2429.4	2428.9	2434.0	2431.9
7.5°	2301.1	2297.8	2292.7	2304.2	2314.9
10°	2082.2	2078.5	2067.5	2072.9	2081.7
12.5°	1759.0	1747.0	1746.8	1764.1	1761.8
15°	1332.5	1316.4	1325.3	1321.0	1318.6
17.5°	896.0	889.8	901.7	898.2	882.7
20°	644.6	646.2	668.7	657.4	643.7
22.5°	470.3	476.2	502.9	473.7	462.9
25°	313.2	325.0	353.1	316.7	306.8
27.5°	192.6	198.0	226.5	190.2	184.7
30°	119.8	117.1	130.5	112.0	104.4
32.5°	78.6	75.2	79.5	71.3	65.1
35°	52.5	53.7	50.4	50.0	42.2
37.5°	32.8	37.8	33.3	35.5	27.2
40°	21.2	27.4	23.5	26.0	20.0
42.5°	17.4	21.1	19.4	20.6	17.8
45°	13.8	17.1	17.1	17.1	13.9
47.5°	7.7	11.5	14.7	11.7	8.1
50°	4.3	5.8	11.3	6.1	4.6
52.5°	3.0	3.3	7.8	3.4	3.1
55°	2.2	2.3	4.2	2.5	2.3
57.5°	1.7	1.8	2.2	1.8	1.7
60°	1.4	1.4	1.6	1.5	1.4
62.5°	1.0	1.0	1.1	1.0	1.0
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.3	0.5	0.5	0.5	0.5
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)