

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779356

Luminaire Tested: LER4D08D010-EC4DR550210IC9024-4LBS1B

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P779356  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER4D08D010-EC4DR550210IC9024-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 55° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 658.9 lumens  
Efficiency: N/A  
Efficacy: 74.0 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P779356

CATALOG NUMBER: LER4D08D010-EC4DR550210IC9024-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P779356

CATALOG NUMBER: LER4D08D010-EC4DR550210IC9024-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 94  |    |    |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 95  | 98  | 95  | 92  | 95  | 93  | 90  | 92  | 90  | 89  | 87  |    |    |
| 3   | 102 | 96  | 91  | 87  | 100 | 95  | 90  | 86  | 92  | 88  | 85  | 90  | 86  | 84  | 87  | 85  | 82  | 81  |    |    |
| 4   | 97  | 90  | 84  | 80  | 95  | 88  | 83  | 79  | 86  | 82  | 78  | 84  | 81  | 78  | 82  | 79  | 77  | 75  |    |    |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 77  | 73  | 81  | 76  | 73  | 79  | 75  | 72  | 78  | 74  | 71  | 70  |    |    |
| 6   | 88  | 79  | 73  | 68  | 86  | 78  | 72  | 68  | 76  | 71  | 68  | 75  | 70  | 67  | 74  | 70  | 67  | 65  |    |    |
| 7   | 83  | 74  | 68  | 64  | 82  | 73  | 67  | 63  | 72  | 67  | 63  | 71  | 66  | 63  | 70  | 65  | 62  | 61  |    |    |
| 8   | 79  | 69  | 63  | 59  | 78  | 69  | 63  | 59  | 68  | 63  | 59  | 67  | 62  | 59  | 66  | 62  | 58  | 57  |    |    |
| 9   | 75  | 66  | 60  | 56  | 74  | 65  | 59  | 55  | 64  | 59  | 55  | 63  | 58  | 55  | 62  | 58  | 55  | 54  |    |    |
| 10  | 72  | 62  | 56  | 52  | 71  | 61  | 56  | 52  | 61  | 56  | 52  | 60  | 55  | 52  | 59  | 55  | 52  | 50  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 80722 |
| 5°  | 77510 |
| 10° | 77219 |
| 15° | 75007 |
| 20° | 67252 |
| 25° | 55588 |
| 30° | 41987 |
| 35° | 30438 |
| 40° | 19483 |
| 45° | 8900  |
| 50° | 2907  |
| 55° | 1257  |
| 60° | 546   |
| 65° | 78    |
| 70° | 0     |
| 75° | 0     |
| 80° | 0     |
| 85° | 0     |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8900 cd/sqm



TEST NUMBER: P779356

CATALOG NUMBER: LER4D08D010-EC4DR550210IC9024-4LBS1B

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 67.2   | 10.2      |
| 10°-20°   | 183.5  | 27.9      |
| 20°-30°   | 209.2  | 31.7      |
| 30°-40°   | 142.4  | 21.6      |
| 40°-50°   | 49.1   | 7.5       |
| 50°-60°   | 6.8    | 1.0       |
| 60°-70°   | 0.7    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 460.0  | 69.8      |
| 0°-40°    | 602.3  | 91.4      |
| 0°-60°    | 658.2  | 99.9      |
| 0°-90°    | 658.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 658.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 739 |      |
| 5°  | 707 | 67   |
| 15° | 663 | 184  |
| 25° | 461 | 209  |
| 35° | 228 | 142  |
| 45° | 58  | 49   |
| 55° | 7   | 7    |
| 65° | 0   | 1    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P779356

CATALOG NUMBER: LER4D08D010-EC4DR550210IC9024-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 738.8 |
| 2.5°  | 721.9 |
| 5°    | 706.7 |
| 7.5°  | 699.3 |
| 10°   | 696.0 |
| 12.5° | 685.0 |
| 15°   | 663.1 |
| 17.5° | 628.2 |
| 20°   | 578.4 |
| 22.5° | 520.9 |
| 25°   | 461.1 |
| 27.5° | 398.7 |
| 30°   | 332.8 |
| 32.5° | 276.9 |
| 35°   | 228.2 |
| 37.5° | 181.9 |
| 40°   | 136.6 |
| 42.5° | 94.7  |
| 45°   | 57.6  |
| 47.5° | 31.1  |
| 50°   | 17.1  |
| 52.5° | 10.1  |
| 55°   | 6.6   |
| 57.5° | 4.2   |
| 60°   | 2.5   |
| 62.5° | 1.1   |
| 65°   | 0.3   |
| 67.5° | 0.1   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)