

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778628

Luminaire Tested: LER4D02D010-EC4DR300210IC9040-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P778628
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D02D010-EC4DR300210IC9040-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 364.4 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778628

CATALOG NUMBER: LER4D02D010-EC4DR300210IC9040-4LBS1B

Luminous Intensity Polar Plot



TEST NUMBER: P778628

CATALOG NUMBER: LER4D02D010-EC4DR300210IC9040-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	98	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	89686	89686	89686
5°	87109	87009	87116
10°	75455	74918	75431
15°	49226	48965	48719
20°	24477	25398	24445
25°	12331	13910	12077
30°	4941	5374	4295
35°	2289	2196	1841
40°	989	1099	929
45°	693	866	704
50°	238	631	250
55°	133	254	147
60°	92	107	92
65°	54	54	54
70°	45	22	45
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 866 cd/sqm



TEST NUMBER: P778628

CATALOG NUMBER: LER4D02D010-EC4DR300210IC9040-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.0	28.3
10°-20°	165.9	45.5
20°-30°	71.7	19.7
30°-40°	16.3	4.5
40°-50°	5.6	1.5
50°-60°	1.4	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.7	93.5
0°-40°	357.0	98.0
0°-60°	364.0	99.9
0°-90°	364.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	364.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1172	1172	1172	1172	1172	
5°	1134	1133	1132	1135	1134	103
15°	621	614	618	616	615	166
25°	146	152	165	148	143	70
35°	24	25	24	23	20	17
45°	6	8	8	8	6	5
55°	1	1	2	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P778628

CATALOG NUMBER: LER4D02D010-EC4DR300210IC9040-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1171.7	1171.7	1171.7	1171.7	1171.7
2.5°	1163.9	1163.1	1163.5	1164.1	1164.4
5°	1133.7	1132.6	1132.4	1134.7	1133.8
7.5°	1072.8	1071.2	1068.9	1074.2	1079.3
10°	970.8	969.0	963.9	966.5	970.5
12.5°	820.1	814.5	814.4	822.5	821.3
15°	621.2	613.7	617.9	615.9	614.8
17.5°	417.7	414.9	420.4	418.7	411.6
20°	300.5	301.3	311.8	306.5	300.1
22.5°	219.3	222.0	234.5	220.8	215.8
25°	146.0	151.5	164.7	147.6	143.0
27.5°	89.8	92.3	105.6	88.6	86.1
30°	55.9	54.6	60.8	52.3	48.6
32.5°	36.7	35.0	37.1	33.2	30.4
35°	24.5	25.0	23.5	23.3	19.7
37.5°	15.3	17.6	15.5	16.6	12.7
40°	9.9	12.8	11.0	12.1	9.3
42.5°	8.1	9.9	9.1	9.6	8.3
45°	6.4	8.0	8.0	8.0	6.5
47.5°	3.6	5.3	6.8	5.4	3.8
50°	2.0	2.7	5.3	2.8	2.1
52.5°	1.4	1.5	3.6	1.6	1.4
55°	1.0	1.1	1.9	1.1	1.1
57.5°	0.8	0.9	1.0	0.9	0.8
60°	0.6	0.6	0.7	0.7	0.6
62.5°	0.5	0.5	0.5	0.5	0.5
65°	0.3	0.3	0.3	0.3	0.3
67.5°	0.2	0.2	0.2	0.2	0.2
70°	0.2	0.1	0.1	0.1	0.2
72.5°	0.1	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)