

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779440

Luminaire Tested: LER4D08D010-EC4DR700210IC9035-4LBS1B

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P779440  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER4D08D010-EC4DR700210IC9035-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 780.5 lumens  
Efficiency: N/A  
Efficacy: 87.7 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P779440

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9035-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P779440

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9035-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 97  | 94  | 105 | 100 | 96  | 92  | 97  | 93  | 90  |  | 94  | 91  | 88  |  | 91  |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 85  | 82  |  | 87  | 84  | 81  |  | 85  |
| 4   | 95  | 87  | 81  | 76  | 93  | 86  | 80  | 76  | 83  | 78  | 75  |  | 81  | 77  | 74  |  | 79  |
| 5   | 89  | 80  | 74  | 69  | 88  | 79  | 73  | 69  | 78  | 72  | 68  |  | 76  | 71  | 68  |  | 74  |
| 6   | 84  | 75  | 68  | 63  | 83  | 74  | 68  | 63  | 72  | 67  | 63  |  | 71  | 66  | 62  |  | 69  |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 62  | 58  | 67  | 62  | 58  |  | 66  | 61  | 57  |  | 65  |
| 8   | 75  | 65  | 58  | 54  | 74  | 64  | 58  | 54  | 63  | 57  | 53  |  | 62  | 57  | 53  |  | 61  |
| 9   | 71  | 61  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 50  |  | 58  | 53  | 49  |  | 57  |
| 10  | 67  | 57  | 50  | 46  | 66  | 56  | 50  | 46  | 55  | 50  | 46  |  | 55  | 50  | 46  |  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 67305 |
| 5°  | 67134 |
| 10° | 66989 |
| 15° | 66975 |
| 20° | 66322 |
| 25° | 62303 |
| 30° | 55550 |
| 35° | 44283 |
| 40° | 29396 |
| 45° | 17584 |
| 50° | 9111  |
| 55° | 4800  |
| 60° | 1683  |
| 65° | 26    |
| 70° | 0     |
| 75° | 0     |
| 80° | 0     |
| 85° | 0     |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17584 cd/sqm

TEST NUMBER: P779440

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9035-4LBS1B

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 58.2   | 7.5       |
| 10°-20°   | 167.0  | 21.4      |
| 20°-30°   | 235.5  | 30.2      |
| 30°-40°   | 203.3  | 26.1      |
| 40°-50°   | 91.0   | 11.7      |
| 50°-60°   | 23.8   | 3.1       |
| 60°-70°   | 1.6    | 0.2       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 460.7  | 59.0      |
| 0°-40°    | 664.1  | 85.1      |
| 0°-60°    | 778.9  | 99.8      |
| 0°-90°    | 780.5  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 780.5  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 616 |      |
| 5°  | 612 | 58   |
| 15° | 592 | 167  |
| 25° | 517 | 236  |
| 35° | 332 | 203  |
| 45° | 114 | 91   |
| 55° | 25  | 24   |
| 65° | 0   | 2    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P779440

CATALOG NUMBER: LER4D08D010-EC4DR700210IC9035-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 616.0 |
| 2.5°  | 615.3 |
| 5°    | 612.1 |
| 7.5°  | 609.5 |
| 10°   | 603.8 |
| 12.5° | 598.7 |
| 15°   | 592.1 |
| 17.5° | 584.5 |
| 20°   | 570.4 |
| 22.5° | 547.2 |
| 25°   | 516.8 |
| 27.5° | 481.5 |
| 30°   | 440.3 |
| 32.5° | 389.8 |
| 35°   | 332.0 |
| 37.5° | 268.2 |
| 40°   | 206.1 |
| 42.5° | 156.6 |
| 45°   | 113.8 |
| 47.5° | 78.4  |
| 50°   | 53.6  |
| 52.5° | 37.0  |
| 55°   | 25.2  |
| 57.5° | 15.2  |
| 60°   | 7.7   |
| 62.5° | 2.5   |
| 65°   | 0.1   |
| 67.5° | 0.0   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)