

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778729

Luminaire Tested: LER4D02D010-EC4DR500210IC9050-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P778729
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D02D010-EC4DR500210IC9050-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 408.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778729

CATALOG NUMBER: LER4D02D010-EC4DR500210IC9050-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P778729

CATALOG NUMBER: LER4D02D010-EC4DR500210IC9050-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95						
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90						
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85						
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80						
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76						
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72						
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69						
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65						
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62						
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71817
5°	71071
10°	69907
15°	63650
20°	52962
25°	37601
30°	19896
35°	8110
40°	3009
45°	1375
50°	561
55°	286
60°	153
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1375 cd/sqm



TEST NUMBER: P778729

CATALOG NUMBER: LER4D02D010-EC4DR500210IC9050-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.3	15.0
10°-20°	154.8	37.9
20°-30°	139.0	34.1
30°-40°	43.5	10.7
40°-50°	7.6	1.9
50°-60°	1.5	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.1	87.0
0°-40°	398.6	97.7
0°-60°	407.7	99.9
0°-90°	408.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	408.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	657	
5°	648	61
15°	563	155
25°	312	139
35°	61	44
45°	9	8
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P778729

CATALOG NUMBER: LER4D02D010-EC4DR500210IC9050-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	657.3
2.5°	654.1
5°	648.0
7.5°	638.7
10°	630.1
12.5°	602.3
15°	562.7
17.5°	512.4
20°	455.5
22.5°	389.7
25°	311.9
27.5°	229.3
30°	157.7
32.5°	102.7
35°	60.8
37.5°	34.9
40°	21.1
42.5°	13.8
45°	8.9
47.5°	5.4
50°	3.3
52.5°	2.3
55°	1.5
57.5°	1.0
60°	0.7
62.5°	0.4
65°	0.2
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)