

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778760

Luminaire Tested: LER4D02D010-EC4DR600210IC9027-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P778760
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D02D010-EC4DR600210IC9027-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 333.9 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778760

CATALOG NUMBER: LER4D02D010-EC4DR600210IC9027-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P778760

CATALOG NUMBER: LER4D02D010-EC4DR600210IC9027-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	87	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	63		82	73	67	63		72	67	63		71	66	63		69	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	61	58
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	55	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36504
5°	36413
10°	37622
15°	37667
20°	34649
25°	29476
30°	22457
35°	15886
40°	9328
45°	3770
50°	1258
55°	610
60°	240
65°	26
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3770 cd/sqm



TEST NUMBER: P778760

CATALOG NUMBER: LER4D02D010-EC4DR600210IC9027-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.0	9.6
10°-20°	92.2	27.6
20°-30°	110.4	33.1
30°-40°	73.9	22.1
40°-50°	21.9	6.6
50°-60°	3.2	0.9
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	234.7	70.3
0°-40°	308.5	92.4
0°-60°	333.6	99.9
0°-90°	333.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	333.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	334	
5°	332	32
15°	333	92
25°	244	110
35°	119	74
45°	24	22
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P778760

CATALOG NUMBER: LER4D02D010-EC4DR600210IC9027-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	334.1
2.5°	333.7
5°	332.0
7.5°	336.6
10°	339.1
12.5°	338.7
15°	333.0
17.5°	319.6
20°	298.0
22.5°	272.2
25°	244.5
27.5°	213.3
30°	178.0
32.5°	146.6
35°	119.1
37.5°	91.6
40°	65.4
42.5°	43.1
45°	24.4
47.5°	12.5
50°	7.4
52.5°	4.8
55°	3.2
57.5°	2.1
60°	1.1
62.5°	0.5
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)