

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779585

Luminaire Tested: LER4D10D010-EC4DR350210IC9035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779585
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D10D010-EC4DR350210IC9035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1060.8 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779585

CATALOG NUMBER: LER4D10D010-EC4DR350210IC9035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P779585

CATALOG NUMBER: LER4D10D010-EC4DR350210IC9035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	94	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	77	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318888
5°	311387
10°	280650
15°	217826
20°	123552
25°	48066
30°	17928
35°	9830
40°	6418
45°	3909
50°	2499
55°	1753
60°	1289
65°	698
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3909 cd/sqm



TEST NUMBER: P779585

CATALOG NUMBER: LER4D10D010-EC4DR350210IC9035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.1	24.6
10°-20°	509.8	48.1
20°-30°	207.9	19.6
30°-40°	49.8	4.7
40°-50°	20.7	2.0
50°-60°	8.6	0.8
60°-70°	2.7	0.3
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	978.9	92.3
0°-40°	1028.6	97.0
0°-60°	1058.0	99.7
0°-90°	1060.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1060.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2919	
5°	2839	261
15°	1926	510
25°	399	208
35°	74	50
45°	25	21
55°	9	9
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779585

CATALOG NUMBER: LER4D10D010-EC4DR350210IC9035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2918.6
2.5°	2901.1
5°	2839.1
7.5°	2715.7
10°	2529.6
12.5°	2267.6
15°	1925.7
17.5°	1507.6
20°	1062.6
22.5°	677.6
25°	398.7
27.5°	225.4
30°	142.1
32.5°	99.8
35°	73.7
37.5°	57.0
40°	45.0
42.5°	34.7
45°	25.3
47.5°	19.0
50°	14.7
52.5°	11.6
55°	9.2
57.5°	7.5
60°	5.9
62.5°	4.3
65°	2.7
67.5°	1.0
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)