

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779727

Luminaire Tested: LER4D10D010-EC4DR650210IC9030-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P779727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D10D010-EC4DR650210IC9030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 875.9 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779727

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9030-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P779727

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46449
5°	46333
10°	46293
15°	44864
20°	40846
25°	35591
30°	29599
35°	23457
40°	16933
45°	10696
50°	5579
55°	2963
60°	1554
65°	857
70°	359
75°	406
80°	269
85°	201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10696 cd/sqm



TEST NUMBER: P779727

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.2	8.6
10°-20°	206.0	23.5
20°-30°	251.7	28.7
30°-40°	204.3	23.3
40°-50°	101.8	11.6
50°-60°	28.4	3.2
60°-70°	6.5	0.7
70°-80°	1.7	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.9	60.8
0°-40°	737.2	84.2
0°-60°	867.4	99.0
0°-90°	875.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	795	
5°	790	75
15°	742	206
25°	552	252
35°	329	204
45°	130	102
55°	29	28
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P779727

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	795.3
2.5°	794.7
5°	790.3
7.5°	787.7
10°	780.6
12.5°	766.1
15°	742.0
17.5°	704.4
20°	657.2
22.5°	606.2
25°	552.3
27.5°	494.7
30°	438.9
32.5°	383.9
35°	329.0
37.5°	274.2
40°	222.1
42.5°	173.2
45°	129.5
47.5°	90.2
50°	61.4
52.5°	42.3
55°	29.1
57.5°	19.7
60°	13.3
62.5°	9.2
65°	6.2
67.5°	3.2
70°	2.1
72.5°	2.0
75°	1.8
77.5°	1.1
80°	0.8
82.5°	0.6
85°	0.3
87.5°	0.2
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)