

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779736

Luminaire Tested: LER4D10D010-EC4DR650210IC9050-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P779736
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D10D010-EC4DR650210IC9050-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 917.5 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779736

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9050-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P779736

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9050-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48656
5°	48531
10°	48494
15°	46999
20°	42786
25°	37286
30°	31008
35°	24569
40°	17734
45°	11200
50°	5842
55°	3106
60°	1635
65°	898
70°	376
75°	406
80°	303
85°	201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11200 cd/sqm



TEST NUMBER: P779736

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9050-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.8	8.6
10°-20°	215.7	23.5
20°-30°	263.7	28.7
30°-40°	214.0	23.3
40°-50°	106.6	11.6
50°-60°	29.8	3.2
60°-70°	6.8	0.7
70°-80°	1.8	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.2	60.8
0°-40°	772.2	84.2
0°-60°	908.6	99.0
0°-90°	917.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	917.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	833	
5°	828	79
15°	777	216
25°	579	264
35°	345	214
45°	136	107
55°	30	30
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P779736

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9050-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	833.1
2.5°	832.4
5°	827.8
7.5°	825.1
10°	817.7
12.5°	802.5
15°	777.3
17.5°	737.8
20°	688.4
22.5°	635.0
25°	578.6
27.5°	518.2
30°	459.8
32.5°	402.2
35°	344.6
37.5°	287.2
40°	232.6
42.5°	181.5
45°	135.6
47.5°	94.5
50°	64.3
52.5°	44.3
55°	30.5
57.5°	20.6
60°	14.0
62.5°	9.7
65°	6.5
67.5°	3.3
70°	2.2
72.5°	2.1
75°	1.8
77.5°	1.2
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.2
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)