

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778793

Luminaire Tested: LER4D02D010-EC4DR650210IC9035-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P778793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D02D010-EC4DR650210IC9035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 339.4 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778793

CATALOG NUMBER: LER4D02D010-EC4DR650210IC9035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P778793

CATALOG NUMBER: LER4D02D010-EC4DR650210IC9035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17994
5°	17952
10°	17934
15°	17377
20°	15824
25°	13790
30°	11471
35°	9090
40°	6564
45°	4146
50°	2162
55°	1151
60°	607
65°	332
70°	137
75°	158
80°	101
85°	67

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4146 cd/sqm



TEST NUMBER: P778793

CATALOG NUMBER: LER4D02D010-EC4DR650210IC9035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.1	8.6
10°-20°	79.8	23.5
20°-30°	97.5	28.7
30°-40°	79.1	23.3
40°-50°	39.4	11.6
50°-60°	11.0	3.2
60°-70°	2.5	0.7
70°-80°	0.6	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	206.5	60.8
0°-40°	285.6	84.2
0°-60°	336.1	99.0
0°-90°	339.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	339.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	308	
5°	306	29
15°	287	80
25°	214	98
35°	128	79
45°	50	39
55°	11	11
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P778793

CATALOG NUMBER: LER4D02D010-EC4DR650210IC9035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	308.1
2.5°	307.9
5°	306.2
7.5°	305.2
10°	302.4
12.5°	296.8
15°	287.4
17.5°	272.9
20°	254.6
22.5°	234.9
25°	214.0
27.5°	191.7
30°	170.1
32.5°	148.7
35°	127.5
37.5°	106.2
40°	86.1
42.5°	67.1
45°	50.2
47.5°	34.9
50°	23.8
52.5°	16.4
55°	11.3
57.5°	7.6
60°	5.2
62.5°	3.6
65°	2.4
67.5°	1.2
70°	0.8
72.5°	0.7
75°	0.7
77.5°	0.5
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)