

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779737

Luminaire Tested: LER4D10D010-EC4DR650210IC9050-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P779737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D10D010-EC4DR650210IC9050-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 988.2 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779737

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9050-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P779737

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9050-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52400
5°	52272
10°	52230
15°	50615
20°	46080
25°	40154
30°	33403
35°	26466
40°	19106
45°	12067
50°	6288
55°	3340
60°	1752
65°	967
70°	393
75°	451
80°	303
85°	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12067 cd/sqm



TEST NUMBER: P779737

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9050-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.9	8.6
10°-20°	232.4	23.5
20°-30°	284.0	28.7
30°-40°	230.5	23.3
40°-50°	114.8	11.6
50°-60°	32.0	3.2
60°-70°	7.3	0.7
70°-80°	1.9	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	601.2	60.8
0°-40°	831.7	84.2
0°-60°	978.6	99.0
0°-90°	988.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	988.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	897	
5°	892	85
15°	837	232
25°	623	284
35°	371	230
45°	146	115
55°	33	32
65°	7	7
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P779737

CATALOG NUMBER: LER4D10D010-EC4DR650210IC9050-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	897.2
2.5°	896.6
5°	891.6
7.5°	888.7
10°	880.7
12.5°	864.3
15°	837.1
17.5°	794.7
20°	741.4
22.5°	683.9
25°	623.1
27.5°	558.1
30°	495.3
32.5°	433.2
35°	371.2
37.5°	309.3
40°	250.6
42.5°	195.4
45°	146.1
47.5°	101.8
50°	69.2
52.5°	47.7
55°	32.8
57.5°	22.2
60°	15.0
62.5°	10.4
65°	7.0
67.5°	3.6
70°	2.3
72.5°	2.2
75°	2.0
77.5°	1.3
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)