

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P779762

Luminaire Tested: LER4D10D010-EC4DR700210IC9050-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P779762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER4D10D010-EC4DR700210IC9050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1195.3 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P779762

CATALOG NUMBER: LER4D10D010-EC4DR700210IC9050-4LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P779762

CATALOG NUMBER: LER4D10D010-EC4DR700210IC9050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103077
5°	102823
10°	102603
15°	102573
20°	101564
25°	95408
30°	85059
35°	67812
40°	45042
45°	26917
50°	13955
55°	7334
60°	2600
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26917 cd/sqm



TEST NUMBER: P779762

CATALOG NUMBER: LER4D10D010-EC4DR700210IC9050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.2	7.5
10°-20°	255.7	21.4
20°-30°	360.7	30.2
30°-40°	311.4	26.1
40°-50°	139.4	11.7
50°-60°	36.5	3.1
60°-70°	2.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	705.6	59.0
0°-40°	1017.0	85.1
0°-60°	1192.9	99.8
0°-90°	1195.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1195.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	943	
5°	938	89
15°	907	256
25°	791	361
35°	508	311
45°	174	139
55°	38	37
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P779762

CATALOG NUMBER: LER4D10D010-EC4DR700210IC9050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	943.4
2.5°	942.4
5°	937.5
7.5°	933.5
10°	924.8
12.5°	917.0
15°	906.8
17.5°	895.1
20°	873.5
22.5°	838.1
25°	791.4
27.5°	737.3
30°	674.2
32.5°	597.0
35°	508.4
37.5°	410.7
40°	315.8
42.5°	239.9
45°	174.2
47.5°	120.1
50°	82.1
52.5°	56.7
55°	38.5
57.5°	23.3
60°	11.9
62.5°	3.7
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)